

Cable, Cord and Hose Reels



Features and Benefits

inREACH™ Industrial Cord Reels

- Durable, corrosion resistant cast aluminum construction
- Multi-position guide arm can be mounted in two positions
- Ratchet lock can be disengaged in field for constant tension applications

Labor Savings are inREACH™!



inREACH™ Industrial Cord Reels Connector Ends

Description	Amps	Volts AC	Cable Length Feet (m)	Cable Type	Weight Lbs. (kg)	Catalog Number
White Industrial Reel	with HBL5269C	15	125	45 (13.7)	14/3 SJO	24.0 (10.9) HBLI45143C15
	with HBL5369C	20	125	45 (13.7)	12/3 SJO	26.5 (12.0) HBLI45123C20
	with HBL2313					26.5 (12.0) HBLI45123TL20
White Industrial Reel with Yellow Portable Outlet Box	(1) 15A Duplex Receptacle	15	125	45 (13.7)	14/3 SJO	26.5 (12.0) HBLI45143R15
	(2) 15A Duplex Receptacles					26.5 (12.0) HBLI45143R215
	GFCI Module and (1) 15A Duplex Receptacle	15	125	45 (13.7)	14/3 SJO	26.5 (12.0) HBLI45143GF15
White Industrial Reel with Black Portable Outlet Box	GFCI Module and (2) 15A Duplex Receptacles					26.5 (12.0) HBLI45143GF215
	(1) 15A Duplex Receptacle	15	125	45 (13.7)	14/3 SJO	26.5 (12.0) HBLI45143R15M1
White Industrial Reel with Yellow Portable Outlet Box	(2) 15A Duplex Receptacles					26.5 (12.0) HBLI45143R215M1
	GFCI Module and (2) 15A Duplex Receptacles	15	125	45 (13.7)	14/3 SJO	26.5 (12.0) HBLI45143GF215M1
White Industrial Reel with Yellow Portable Outlet Box	(1) 20A Duplex Receptacle	20	125	45 (13.7)	12/3 SJO	26.5 (12.0) HBLI45123R20
	(2) 20A Duplex Receptacles					26.5 (12.0) HBLI45123R220
	GFCI Module and (1) 20A Duplex Receptacle	20	125	45 (13.7)	12/3 SJO	26.5 (12.0) HBLI45123GF20
White Industrial Reel with Black Portable Outlet Box	GFCI Module and (2) 20A Duplex Receptacles					26.5 (12.0) HBLI45123GF220
	(1) 20A Duplex Receptacle	20	125	45 (13.7)	12/3 SJO	26.5 (12.0) HBLI45123R20M1
White Industrial Reel with Black Portable Outlet Box	(2) 20A Duplex Receptacles					26.5 (12.0) HBLI45123R220M1
	GFCI Module and (2) 20A Duplex Receptacles	20	125	45 (13.7)	12/3 SJO	26.5 (12.0) HBLI45123GF220M1
White Industrial Reel with Triple Tap Outlet	GFCI Module and Triple Tap Outlet	15	125	45 (13.7)	12/3 SJO	26.5 (12.0) HBLI45123GFTT



HBLI45123R20



HBLI45123GF20



HBLI45123GF220M1

Note: 15A reels are supplied with HBL5266C on the power supply cord. 20A reels are supplied with HBL5366C on the power supply cord. For shorter cable lengths, modify length indication in catalog number (i.e. HBLIXX); 35ft & 25ft lengths are available. For yellow reel, add 'Y' suffix to catalog number.

inREACH™ Accessories

Description	Weight Lbs. (kg)	Catalog Number
Mounting bracket	2.5 (1.1)	HBLIMB
Mounting bracket with junction box mount	3.0 (1.4)	HBLIMBJ
Mounting bracket	3.5 (1.6)	HBLIACCMB*
Mounting bracket with junction box mount	4.0 (1.8)	HBLIACCMBJ*
340° pivot base	3.5 (1.1)	HBLI340PB
Replacement stop.	.2 (.09)	HBLI16BS HBLI14BS HBLI12BS HBLI10BS

Note: *Compatible with cord reel models from page J-2 marked with a single asterisk (*)

Plenum Rated Enclosure for inREACH™ Cord Reels

Description	Weight lbs. (kg)	Catalog Number
Plenum Rated Enclosure	30 lbs. (13.6)	HBLIPRBOX

Note: Check with manufacturer for compatible cord reel models.



HBLIMB



HBLIMBJ



HBLI340PB



HBLI16BS



HBLI14BS



HBLIPRBOX