

# Cable, Cord and Hose Reels



## inREACH™ Medical Cord Reels



HBLIWC45123GF220HG

Description	Amps	Volts	Cable Length Feet (m)	Cable Type	Weight Lbs. (kg)	Catalog Number
White reel, white portable outlet box, GFCI module, and (2) 20A Hospital Grade receptacles	20A	125V AC	45 (13.7)	12/3 SJO	34.9 (15.8)	<b>HBLIWC45123GF220HG</b>
White reel, white portable outlet box, and (2) 20A Hospital Grade receptacles	20A	125V AC	45 (13.7)	12/3 SJO	34.4 (15.6)	<b>HBLIWC45123R220HG</b>
White reel and Hospital Grade connector HBL8319C	20A	125V AC	45 (13.7)	12/3 SJO	33.6 (15.2)	<b>HBLIWC45123C20HG</b>



HBLI45163LED

## Industrial Lighted Cord Reels, 45 Ft. (13.7m) - 16/3 AWG SJEO Cable



Cord End	Amps	Volts AC	Watts (Max)	Weight Lbs. (kg)	Catalog Number
LED hand lamp, with end light, white reel.	0.07	125	8 + 1	22.9 (10.4)	<b>HBLI45163LED</b>
Fluorescent hand lamp, white reel.	0.3	125	13	22.9 (10.4)	<b>HBLI45163FL</b>
Incandescent hand lamp, white reel.	0.8	125	100	22.9 (10.4)	<b>HBLI45163IN</b>

Note: Supplied with 5 ft. power supply cord with HBL5266C, 15A straight blade plug. For shorter cable lengths, modify length indication in catalog number (i.e. HBLIXX); 35ft & 25ft lengths are available. For yellow reel, add 'Y' suffix to catalog number.



HBLI50CAT6

## InREACH™ Category 6 Data Reels

Description	Cable Length ft (m)	Cable Type	Weight lbs. (kg)	Catalog Number
Black Data Reels with RJ45 Plugs	50 (15.2)	Cat 6	22.9 (10.4)	<b>HBLI50CAT6</b>
White Data Reels with RJ45 Plugs	50 (15.2)	Cat 6	22.9 (10.4)	<b>HBLI50CAT6W</b>

## Accessories



HBL16LEDR

Description	Amps	Volts AC	Watts (Max)	Weight Lbs. (kg)	Catalog Number
Replacement stop.	—	—	—	.2 (.09)	<b>HBL16BS</b>
Replacement LED hand lamp.	0.07	120	8 + 1	1 (.5)	<b>HBL16LEDR*</b>
Replacement fluorescent hand lamp.	0.3	120	13	1 (.5)	<b>HBL16FLR</b>
Replacement incandescent hand lamp.	0.8	125	100	1 (.5)	<b>HBL16INR</b>

Note: \*cETLus Listed by INTERTEK.

## Commercial Lighted Cord Reels



Description	Amps	Volts AC	Cable Length Feet (m)	Cable Type	Watts (Max)	Weight Lbs. (kg)	Catalog Number
White Reel with LED hand lamp, with flashlight end.	0.65	125	40 (12.2)	#18/2 SJTOW	8 + 1	8.2 (3.7)	<b>HBLC40182LED</b>
White Reel with non-metallic incandescent hand lamp and automatic shut off switch.	0.6	125	25 (7.6)	#16/3 SJT	75	9.0 (4.1)	<b>HBLC25163AIN**</b>
Yellow Reel with metallic incandescent hand lamp with receptacle.	13	125	25 (7.6)	#14/3 SJT	1,625	9.5 (4.3)	<b>HBLC25143IN</b>

Note: \*\*Allows the electrical cord reel installation to conform to Article 511 of the National Electric Code concerning installation of electrical devices in commercial garages, repair facilities and storage locations by positioning the switch above the defined area where hazardous fumes may collect.



HBLC40182LED



HBLC25143IN

Dimensions in Inches (mm)



INTERTEK and the Intertek logo are registered trademarks of Intertek Group plc.