

Cable, Cord and Hose Reels

Features and Benefits

Tool Balancers



ERGO™ -1
UP TO
5lbs



- Hand-windable spring tension adjustment knob is flush with the housing
- Push-button to easily release spring tension
- Rugged steel upper swivel hook with secondary safety cable provision

ERGO™ -2
UP TO
27lbs



- Rugged steel construction with black polyester baked finish
- Reinforced hanging bracket with forged clevis for ceiling mounting
- Spring is permanently lubricated and adjustable

ERGO™ -3
UP TO
308lbs



- Rugged die cast aluminum housing
- Both top and bottom hooks have spring-loaded safety latches
- Heavy duty steel wire rope

ERGO-1 Light Duty Tool Balancers

Description	Load lbs (kg)		Cable Length* Feet (m)	Reel Weight Lbs. (kg)	Catalog Number
	Min	Max			
Balancer for loads up to 5 lbs	0.5 (0.2)	1.5 (0.7)	6 (1.8)	1.3 (0.6)	HBLBD01
	1.5 (0.5)	3.0 (1.4)	6 (1.8)	1.3 (0.6)	HBLBD03
	3.0 (1.4)	5.0 (2.3)	6 (1.8)	1.5 (0.7)	HBLBD05

*Cable lengths listed are for 'active' or 'working' cable. Includes cable stop and safety hook.

ERGO-2 Medium Duty Tool Balancers

Description	Ratchet Lock	Load lbs (kg)		Cable Length* Feet (m)	Reel Weight Lbs. (kg)	Catalog Number
		Min	Max			
Balancers (constant pull reels) May be adjusted to balance through 6-18 in. (152-457mm) range.	No	3 (1.4)	7 (3.2)	8 (2.4)	6 (2.7)	HBLBG03
		5 (2.3)	10 (4.5)	8 (2.4)	6 (2.7)	HBLBG07
		8 (3.6)	12 (5.4)	8 (2.4)	7 (3.2)	HBLBG10
		10 (4.5)	15 (6.8)	8 (2.4)	8 (3.6)	HBLBG15
		16 (7.2)	23 (10.4)	8 (2.4)	8 (3.6)	HBLBG20
		16 (7.2)	23 (10.4)	8 (2.4)	8 (3.6)	HBLBG20SH**
		22 (9.9)	27 (12.2)	8 (2.4)	8 (3.6)	HBLBG25
Retractors (ratchet lock) Retract tool upward when manually released	Yes	3 (1.4)	7 (3.2)	8 (2.4)	6 (2.7)	HBLBG03L
		5 (2.3)	10 (4.5)	8 (2.4)	6 (2.7)	HBLBG07L
		8 (3.6)	12 (5.4)	8 (2.4)	7 (3.2)	HBLBG10L
		10 (4.5)	15 (6.8)	8 (2.4)	8 (3.6)	HBLBG15L
		16 (7.2)	23 (10.4)	8 (2.4)	8 (3.6)	HBLBG20L
		16 (7.2)	23 (10.4)	8 (2.4)	8 (3.6)	HBLBG20LSH**
		22 (9.9)	27 (12.2)	8 (2.4)	8 (3.6)	HBLBG25L
Torque reels*** (ratchet lock and longer cable)	Yes	3 (1.4)	7 (3.2)	15 (4.5)	8 (3.6)	HBLTQ1507
		5 (2.3)	10 (4.5)	15 (4.5)	10 (4.5)	HBLTQ1510
		10 (4.5)	15 (6.8)	15 (4.5)	12 (5.4)	HBLTQ1515

Cable lengths listed are for 'active' or 'working' cable. Includes cable stop and safety hook. | **Includes HBLBGSH "Shock Stop." | *Clevis mount. For rigid mount, add "R" suffix.

ERGO-3 Heavy Duty Tool Balancers

Description	Load lbs (kg)		Cable Length* Feet (m)	Reel Weight Lbs. (kg)	Catalog Number
	Min	Max			
Heavy-duty balancer for loads up to 308 lbs	1.1 (.05)	4.4 (2.0)	3.3 (1.0)	2.2 (1.0)	HBLBH02
	2.2 (1.0)	6.6 (3.0)	4.3 (1.3)	2.8 (1.3)	HBLBH03
	5.5 (2.5)	11 (5.0)	4.3 (1.3)	3.3 (1.5)	HBLBH05
	9.0 (4.1)	20 (9.1)	3.9 (1.2)	13.4 (6.1)	HBLBH09
	20 (9.1)	33 (15.0)	3.9 (1.2)	13.4 (6.1)	HBLBH15
	33 (15.0)	48 (21.8)	4.5 (1.4)	22.6 (10.3)	HBLBH22
	48 (21.8)	66 (30.0)	4.5 (1.4)	22.6 (10.3)	HBLBH30
	66 (30.0)	88 (40.0)	4.5 (1.4)	27.0 (12.2)	HBLBH40
	88 (40.0)	110 (50.0)	4.5 (1.4)	27.0 (12.2)	HBLBH50
	110 (50.0)	132 (60.0)	4.5 (1.4)	31.4 (14.2)	HBLBH60
	132 (60.0)	154 (70.0)	4.5 (1.4)	31.4 (14.2)	HBLBH70
	154 (70.0)	187 (85.0)	4.5 (1.4)	58.4 (26.5)	HBLBH85
	187 (85.0)	220 (100.0)	4.5 (1.4)	56.0 (25.4)	HBLBH100
	220 (100.0)	264 (120.0)	4.5 (1.4)	60.0 (27.2)	HBLBH120
	264 (120.0)	308 (140.0)	4.5 (1.4)	61.0 (27.7)	HBLBH140

**Load includes hose or cord and other attachments which must be supported by balancer. | **Cable lengths listed are for 'active' or 'working' cable. Includes cable stop and safety hook.



Dimensions in Inches (mm)