

Features and Benefits

Commercial Tamper and Weather Resistant GFCI Receptacles

- Patented shutter design for tamper-resistant protection
- Meets NEC® requirements for TR (517-18c) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® self test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired


GFTWRST83WIG

15A 125V
NEMA 5-15R
UL CSA
0.5 HP

20A 125V
NEMA 5-20R
UL CSA
1 HP


Hospital Grade • Tamper-Resistant and Weather Resistant GFCI Receptacles

Description	Rating	Color	Catalog Number	
Standard, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple.	15 and 20A 125V AC	Black	GFTWRST82BK	GFTWRST83BK
		Brown	GFTWRST82	GFTWRST83
		Gray	GFTWRST82GY	GFTWRST83GY
		Ivory	GFTWRST82I	GFTWRST83I
		Light Almond	GFTWRST82LA	GFTWRST83LA
		Red	GFTWRST82R	GFTWRST83R
		White	GFTWRST82W	GFTWRST83W
Assembled in USA, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple.	15 and 20A 125V AC	Black	GFTWRST82BKU	GFTWRST83BKU
		Brown	GFTWRST82U	GFTWRST83U
		Gray	GFTWRST82GYU	GFTWRST83GYU
		Ivory	GFTWRST82IU	GFTWRST83IU
		Light Almond	GFTWRST82LAU	GFTWRST83LAU
		Red	GFTWRST82RU	GFTWRST83RU
		White	GFTWRST82WU	GFTWRST83WU
Isolated Ground, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple.	15 and 20A 125V AC	Black	GFTWRST82BKIG	GFTWRST83BKIG
		Brown	GFTWRST82IG	GFTWRST83IG
		Gray	GFTWRST82GYIG	GFTWRST83GYIG
		Ivory	GFTWRST82IIG	GFTWRST83IIG
		Light Almond	GFTWRST82LAIG	GFTWRST83LAIG
		Orange	GFTWRST82ORIG	GFTWRST83ORIG
		Red	GFTWRST82RIG	GFTWRST83RIG
White	GFTWRST82WIG	GFTWRST83WIG		
SNAPConnect®, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple.	15 and 20A 125V AC	Black	GFTWRST82SNAPBK	GFTWRST83SNAPBK
		Brown	GFTWRST82SNAP	GFTWRST83SNAP
		Gray	GFTWRST82SNAPGY	GFTWRST83SNAPGY
		Ivory	GFTWRST82SNAPI	GFTWRST83SNAPI
		Light Almond	GFTWRST82SNAPLA	GFTWRST83SNAPLA
		Red	GFTWRST82SNAPR	GFTWRST83SNAPR
		White	GFTWRST82SNAPW	GFTWRST83SNAPW

Note: GFCI type receptacles should not be used in critical care patient areas or for electrical life support equipment applications because of the possibility of power interruption. All GFCI receptacles are furnished with a matching color thermoplastic wallplate, 20 amp feed-through capability.

See page Tech-10 for Tamper-Resistant and Weather Resistant descriptions.

SNAPConnect® Right Angle Pigtailed Connector

Description	Wire Type	General Use	Assembled in USA
Clear right angle terminal with 6 inch leads #12 AWG THHN/THWN-2; Polycarbonate housing material.	Solid	SNAP1RA	SNAP1RNA
	Stranded	SNAP2RA	SNAP2RNA
Clear right angle terminal with 6 inch leads #12 AWG THHN/THWN-2; Polycarbonate housing material with WAGO terminals.	Solid	SNAP1RAM2	SNAP1RNAM2
	Stranded	SNAP2RAM2	SNAP2RNAM2

Note: For Assembled in USA products, must order connector with NA suffix.

NEC® is a registered trademark of the National Fire Protection Association (NFPA).


GFTWRST82AL

GFTWRST83GYU

GFTWRST82BKIG

GFTWRST83SNAPI

SNAP1RA