

## Features and Benefits

### Commercial Standard Hospital Grade ● GFCI Receptacles

- Fed. Spec UL Listed, Hospital Grade
- Green power indicator and red trip indicator
- Patented AUTOGUARD® self test technology
- Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple



GFRST82WNL



15A 125V  
NEMA 5-15R  
UL CSA  
0.5 HP



20A 125V  
NEMA 5-20R  
UL CSA  
1 HP

### Hospital Grade ● GFCI Receptacles

Description	Rating	Color	Catalog Number	
Standard, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple.	15 and 20A 125V AC	Black	<b>GFRST82BK</b>	<b>GFRST83BK</b>
		Brown	<b>GFRST82</b>	<b>GFRST83</b>
		Gray	<b>GFRST82GY</b>	<b>GFRST83GY</b>
		Ivory	<b>GFRST82I</b>	<b>GFRST83I</b>
		Light Almond	<b>GFRST82LA</b>	<b>GFRST83LA</b>
		Red	<b>GFRST82R</b>	<b>GFRST83R</b>
		White	<b>GFRST82W</b>	<b>GFRST83W</b>
Assembled in USA, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple.	15 and 20A 125V AC	Black	<b>GFRST82BKU</b>	<b>GFRST83BKU</b>
		Brown	<b>GFRST82U</b>	<b>GFRST83U</b>
		Gray	<b>GFRST82GYU</b>	<b>GFRST83GYU</b>
		Ivory	<b>GFRST82IU</b>	<b>GFRST83IU</b>
		Light Almond	<b>GFRST82LAU</b>	<b>GFRST83LAU</b>
		Red	<b>GFRST82RU</b>	<b>GFRST83RU</b>
		White	<b>GFRST82WU</b>	<b>GFRST83WU</b>
Night Light Two LED Night Lights, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple.	15 and 20A 125V AC	Black	<b>GFRST82BKNL</b>	<b>GFRST83BKNL</b>
		Brown	<b>GFRST82NL</b>	<b>GFRST83NL</b>
		Gray	<b>GFRST82GYNL</b>	<b>GFRST83GYNL</b>
		Ivory	<b>GFRST82INL</b>	<b>GFRST83INL</b>
		Light Almond	<b>GFRST82LANL</b>	<b>GFRST83LANL</b>
		Red	<b>GFRST82RNL</b>	<b>GFRST83RNL</b>
		White	<b>GFRST82WNL</b>	<b>GFRST83WNL</b>
Alarm, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple.	15 and 20A 125V AC	Black	<b>GFRST82BKB</b>	<b>GFRST83BKB</b>
		Brown	<b>GFRST82B</b>	<b>GFRST83B</b>
		Gray	<b>GFRST82GYB</b>	<b>GFRST83GYB</b>
		Ivory	<b>GFRST82IB</b>	<b>GFRST83IB</b>
		Light Almond	<b>GFRST82LAB</b>	<b>GFRST83LAB</b>
		Red	<b>GFRST82RB</b>	<b>GFRST83RB</b>
		White	<b>GFRST82WB</b>	<b>GFRST83WB</b>
SNAPConnect®, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple.	15 and 20A 125V AC	Black	<b>GFRST82SNAPBK</b>	<b>GFRST83SNAPBK</b>
		Brown	<b>GFRST82SNAP</b>	<b>GFRST83SNAP</b>
		Gray	<b>GFRST82SNAPGY</b>	<b>GFRST83SNAPGY</b>
		Ivory	<b>GFRST82SNAPI</b>	<b>GFRST83SNAPI</b>
		Light Almond	<b>GFRST82SNAPLA</b>	<b>GFRST83SNAPLA</b>
		Red	<b>GFRST82SNAPR</b>	<b>GFRST83SNAPR</b>
		White	<b>GFRST82SNAPW</b>	<b>GFRST83SNAPW</b>



GFRST82R



GFRST83INL



GFRST83BKB



GFRST83SNAPGY

Note: GFCI type receptacles should not be used in critical care patient areas or for electrical life support equipment applications because of the possibility of power interruption. All GFCI receptacles are furnished with a matching color thermoplastic wallplate, 20 amp feed-through capability.  
Requires pigtailed connector see page L-14.