

## Hospital Grade ●, HBL® Extra Heavy Duty, Isolated Ground Receptacles




**15A 125V**  
NEMA 5-15R  
UL CSA  
0.5 HP



**20A 125V**  
NEMA 5-20R  
UL CSA  
1 HP

Description	Color	Catalog Number	
Flush, thermoplastic polyester face, duplex, back and side wired, multiple drive screws.	Orange	<b>IG8200</b>	<b>IG8300</b>
	Red	<b>IG8200R</b>	<b>IG8300R</b>
Style Line® decorator.	Orange	—	<b>IG2182</b>
	Ivory	—	<b>IG2182I</b>
	White	—	<b>IG2182WA</b>
Flush, thermoplastic polyester face, single.	Orange	<b>IG8210</b>	<b>IG8310</b>



**IG8200**

## 15A and 20A, 125V HBL® Extra Heavy Duty, Specification Grade, Isolated Ground Receptacles




**15A 125V**  
NEMA 5-15R  
UL CSA  
0.5 HP




**20A 125V**  
NEMA 5-20R  
UL CSA  
1 HP


Description	Color	Catalog Number	
Flush, nylon face, duplex, back and side wired, multiple drive screws.	Orange	<b>IG5262</b>	<b>IG5362</b>
	Gray	<b>IG5262GY</b>	<b>IG5362GY</b>
	Ivory	<b>IG5262I</b>	<b>IG5362I</b>
	Red	<b>IG5262R</b>	<b>IG5362R</b>
	White	—	<b>IG5362W</b>
Weather Resistant, duplex, isolated ground.	Orange	<b>IG5262WR</b>	<b>IG5362WR</b>
	Gray	<b>IG5262GYWR</b>	<b>IG5362GYWR</b>
	Ivory	<b>IG5262IWR</b>	<b>IG5362IWR</b>
	Red	<b>IG5262RWR</b>	<b>IG5362RWR</b>
	White	—	<b>IG5362WWR</b>
Finder groove, nylon face, duplex, back and side wired.	Orange	<b>CR5252IG</b>	<b>CR5352IG</b>
	Black	<b>CR5252IGBK</b>	<b>CR5352IGBK</b>
	Blue	—	<b>CR5352IGBL</b>
	Gray	<b>CR5252IGGY</b>	<b>CR5352IGGY</b>
	Ivory	<b>CR5252IGI</b>	<b>CR5352IGI</b>
	Office White	<b>CR5252IGOW</b>	<b>CR5352IGOW</b>
	White	<b>CR5252IGW</b>	<b>CR5352IGW</b>
Style Line® decorator, flush, nylon face, back and side wired.	Orange	<b>IG2152</b>	<b>IG2162</b>
	Gray	—	<b>IG2162GY</b>
4-PLEX® receptacle.	Orange	<b>IG415</b>	<b>IG420*</b>
Flush, nylon face, single, back and side wired.	Orange	<b>IG5261</b>	<b>IG5361</b>
Weather Resistant, single, Isolated ground.	Orange	<b>IG5261WR</b>	<b>IG5361WR</b>



**IG5262**



**CR5252IG**



**IG415**

Note: \*Not Fed. Spec. Listed.  
See page Tech-10 for Weather Resistant description.  
See page A-47 and A-48 for accessories.  
See page A-28 for 4-PLEX accessories.

Dimensions in Inches (mm)