



Combination Wallplates, 4-Gang

Description	Color	Thermoplastic		Material	Metal Catalog Number
		Standard	Mid-Size		
4-Gang, 3-Toggle, 1-Decorator 	Black	P326BK	—	Aluminum	①
	Brown	P326	—	Brass	①
	Gray	P326GY	—	Brass Plated	①
	Ivory	P326I	—	Chrome	①
	Light Almond	P326LA	—	S/S 302/304	SS326
	White	P326W	—		
4-Gang, 2-Toggle, 2-Decorator 	Ivory	P2262I	—	Aluminum	①
	Light Almond	P2262LA	—	Brass	①
	White	P2262W	—	Brass Plated	①
				Chrome	①
			S/S 302/304	①	

Note: Thermoplastic wallplates feature pre-inserted captive screws for faster assembly in single gang configurations.

① Available as a custom wallplate, see pages N-32 to N-34. Consult custom wallplates section for additional openings and combinations.

Specifications

Listings

Non-Metallic Wallplates	UL Standard 514D
Metallic Wallplates	UL Standard 514D
Certification	UL Files #E31999,E92074
	CSA Standard C22.2 No. 42.1
	CSA File 1733174

Product	Thickness	Mounting Screw(s)	Appearance
Thermoplastic Wallplate	.07 in. (1.8)	Steel (painted slotted screw head).	Smooth satin finish.
302/304 Stainless Steel Wallplate (18% Chromium, 8% Nickel)	.035 in. (0.9) nominal	302/304 stainless steel (18% chromium, 8% nickel). Slotted screw head.	Horizontal brushed finish.
430 Stainless Steel Wallplate (17% Chromium, less than 0.5% Nickel)	.035 in. (0.9) nominal	302/304 stainless steel (17% chromium, less than 0.5% nickel). Slotted screw head.	Horizontal brushed finish.
Brass Wallplate (70% Copper, 30% Zinc)	.04 in. (1.0)	Brass (70% Copper, 30% Zinc). Slotted screw head.	Horizontal brushed finish.
Aluminum Wallplate	.05 in. (1.3)	302/304 stainless steel (17% chromium, less than 0.5% nickel). Slotted screw head.	Horizontal brushed finish.
Brass Plated Steel Wallplate	.03 in. (0.8) nominal	Brass slotted head.	Polished, coated to inhibit oxidation.
Chrome Plated Steel Wallplate	.03 in. (0.8) nominal	302/304 stainless steel (17% chromium, less than 0.5% nickel). Slotted screw head.	Polished, coated to inhibit oxidation.
Steel Painted Wallplate	.03 in. (0.8) nominal	Steel (painted slotted screw head).	Powder coat paint.

Dimensions in Inches (mm)