







Pre-Marked "EMERGENCY" Wallplates

| Description | Color | Thermoplastic | | Material | Metal Catalog Number |
|---|-------|---------------|----------------|--|------------------------------------|
| | | Standard | Mid-Size | | |
| 1-Gang, 1-Duplex, paint filled white lettering  | Red | – | PJ8RMEV | Aluminum Brass Brass Plated Chrome S/S 302/304 | – – – – SS8MEV |
| 1-Gang, 1-Toggle, paint filled white lettering  | Red | – | PJ1RME | Aluminum Brass Brass Plated Chrome S/S 302/304 | – – – – SS1ME |
| 2-Gang, 2 Duplex, paint filled red lettering  | | | | Aluminum Brass Brass Plated Chrome S/S 302/304 | – – – – SS82MEV |

Note: See page N-30 for Mid-Size wallplate dimensions.
All lettering .25 in. (6.3) high.

Pre-Marked "ISOLATED GROUND" Wallplates

| Description | Color | Thermoplastic | | Material | Metal Catalog Number |
|--|--------|----------------|----------|---|----------------------------|
| | | Standard | Mid-Size | | |
| 1-Gang, 1-Duplex, paint filled black  | Orange | P8OIG | – | Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430 | – – – – – – |
| 1-Gang, 1-Single Receptacle 1.40 in. (35.6) Hole for 1.36–1.39 in. (34.5–35.3) Dia. face, paint filled black  | Orange | P7OIG | – | Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430 | – – – – – – |
| 1-Gang, 1-Single Receptacle 1.60 in. (40.6) Hole for 20 and 30A Twist-Lock® with 1.55–1.58 in. (39.4–40.1) Dia. face, paint filled black  | Orange | P720OIG | – | Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430 | – – – – – – |

Dimensions in Inches (mm)