







## Pre-Marked "EMERGENCY" Wallplates

Description	Color	Thermoplastic		Material	Metal Catalog Number
		Standard	Mid-Size		
1-Gang, 1-Duplex, paint filled white lettering 	Red	–	<b>PJ8RMEV</b>	Aluminum Brass Brass Plated Chrome S/S 302/304	– – – – <b>SS8MEV</b>
1-Gang, 1-Toggle, paint filled white lettering 	Red	–	<b>PJ1RME</b>	Aluminum Brass Brass Plated Chrome S/S 302/304	– – – – <b>SS1ME</b>
2-Gang, 2 Duplex, paint filled red lettering 				Aluminum Brass Brass Plated Chrome S/S 302/304	– – – – <b>SS82MEV</b>

Note: See page N-30 for Mid-Size wallplate dimensions.  
All lettering .25 in. (6.3) high.

## Pre-Marked "ISOLATED GROUND" Wallplates

Description	Color	Thermoplastic		Material	Metal Catalog Number
		Standard	Mid-Size		
1-Gang, 1-Duplex, paint filled black 	Orange	<b>P8OIG</b>	–	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	– – – – – –
1-Gang, 1-Single Receptacle 1.40 in. (35.6) Hole for 1.36–1.39 in. (34.5–35.3) Dia. face, paint filled black 	Orange	<b>P7OIG</b>	–	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	– – – – – –
1-Gang, 1-Single Receptacle 1.60 in. (40.6) Hole for 20 and 30A Twist-Lock® with 1.55–1.58 in. (39.4–40.1) Dia. face, paint filled black 	Orange	<b>P720OIG</b>	–	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	– – – – – –

Dimensions in Inches (mm)