

## Weatherproof Thermoplastic Cover For Flanged Inlets and Flanged Receptacles

**IP44**  
SUITABILITY

Description	Catalog Number
For use with 15 and 20A, 2 pole, 2 wire and 2 pole, 3 wire Insulgrip® flanged inlets and flanged receptacles below.	<b>WP1</b>

### Straight Blade, 2 pole, 3 wire Flanged Inlets



HBL5278C  
HBL5378C  
HBL5478C  
HBL5678C

### Flanged Receptacles



HBL5279C  
HBL5379C  
HBL5479C  
HBL5679C

### Twist-Lock®, 2 pole, 2 wire and 2 pole, 3 wire Flanged Inlets



HBL8815C  
HBL7524C  
HBL4716C  
HBL4586C  
HBL4786C

### Flanged Receptacles



HBL8809C  
HBL7526C  
HBL4715C  
HBL4585C  
HBL4785C



## Weatherproof Thermoplastic Cover For Flanged Inlets and Flanged Receptacles

Description	Catalog Number
For use with 20 and 30A, 3, 4, and 5 wire Insulgrip flanged inlets and flanged receptacles below.	<b>WP2</b>

### Twist-Lock®, 2 pole, 3 wire; 3 pole, 4 wire; 4 pole, 4 wire; 4 pole, 5 wire Flanged Inlets



HBL2315	HBL2445	HBL2635	HBL2765
HBL2325	HBL2455	HBL2645	HBL2775
HBL2335	HBL2465	HBL2655	HBL2815
HBL2345	HBL2515	HBL2715	HBL2825
HBL2355	HBL2525	HBL2725	HBL2835
HBL2415	HBL2535	HBL2735	HBL3325C
HBL2425	HBL2615	HBL2745	HBL3334C
HBL2435	HBL2625	HBL2755	HBL7408C

### Flanged Receptacles



HBL2316	HBL2446	HBL2636	HBL2766
HBL2326	HBL2456	HBL2646	HBL2776
HBL2336	HBL2466	HBL2656	HBL2816
HBL2346	HBL2516	HBL2716	HBL2826
HBL2356	HBL2526	HBL2726	HBL2836
HBL2416	HBL2536	HBL2736	HBL3326C
HBL2426	HBL2616	HBL2746	HBL3335C
HBL2436	HBL2626	HBL2756	HBL7409C



WP1



WP2

## Weatherproof Thermoplastic Cover For Flanged Inlets 50 Amp CS Series

Description	Catalog Number
For use with 50A locking inlets with trimmed sides only.	<b>HBL7780</b>



HBL7780