

## **Features and Benefits**

## Weatherproof Non-Metallic While-In-Use Covers

The NEMA 3R Rated EXTRA DUTY® Metallic and Non-metallic While-in-Use Covers offer weather protection for outlets when they are in use.

- Patented keyhole mounting system allows installation in under a minute
- Pre-configured for GFCI with patented technology for alternate devices
- Lockable tab for OSHA compliance
- Sealed-in-place gasket
- High-impact polycarbonate construction provides maximum durability
- Each box contains three or six adapters to make a variety of configurations (16 or 55)



# Weather Resistant Recessed Receptacle with While-In Use Cover

Description	Housing Color	Horizontal Mount	Vertical Mount
Weather and tamper-resistant duplex receptacle with clear while-in-use cover, 15A 125V	GRAY	RW15300GY	RW15400GY
	WHITE	RW15300W	RW15400W
	BROWN	RW15300BR	RW15400BR





RW15300GY



Non-Metallic While-In-Use Covers

Description		Dimensions Height x Width x Depth	Standard	EXTRA DUTY®
Standard 1-gang box with clear tinted cover, for horizontal or vertical mounting; 16-in-1 configurations.	1(16)	5.90" X 4.18" X 2.75" (149.8 X 106.1 X 69.9)	RW57300	RW58300
Extra deep 1-gang box with clear tinted cover, for horizontal or vertical mounting; 16-in-1 configurations.	1(16)	5.92" X 4.20" X 4.75" (150.4 X 106.7 X 120.7)	RW57350	RW58350
Standard 2-gang box, clear tinted cover, for vertical mounting only; 55-in-1 configurations.	1(55) Product Variations	5.54" X 5.43" X 2.75" (140.7 X 138.0 X 69.9)	RW57750	RW58750





RW57350


RW58350






RW57750


RW58750



### **Non-Metallic Cover Dimensions**







RW58750

Dimensions in Inches (mm)

55 Configurations

1 Box {6 Adapters}