











Single 20/30A Twist-Lock® Receptacle Wallplates

Description	Color	Thermoplastic		Material	Metal Catalog Number
		Standard	Mid-Size		
 1-Gang, 1-Single, 1.60 in. (40.6) Dia. Hole	Black	P720BK	-	Aluminum	-
	Brown	P720	-	Brass	SB720
	Gray	P720GY	-	Brass Plated	①
	Ivory	P720I	-	Chrome	①
	Red	P720R	-	S/S 302/304	SS720
White	P720W	-			
 1-Gang, 1-Single, 1.74 in. (44.2) Dia. Hole				Aluminum	-
				Brass	-
				Brass Plated	-
				Chrome	-
				S/S 302/304	SS725
 2-Gang, 1-Single, 1.60 in. (40.6) Dia. Hole				Aluminum	-
				Brass	-
				Brass Plated	-
				Chrome	-
				S/S 302/304	SS749
 3-Gang, 2-Single, 1.60 in. (40.6) Dia. Hole				Aluminum	①
				Brass	①
				Brass Plated	①
				Chrome	①
				S/S 302/304	SS320

Single Receptacle Wallplates

Description	Color	Thermoplastic		Material	Metal Catalog Number
		Standard	Mid-Size		
 1-Gang, 1-Single, 1.97 in. (50.0) Dia. Hole				Aluminum	-
				Brass	-
				Chrome	-
				S/S 302/304	SS737
 1-Gang, 1-Single, 2.16 in. (54.9) Dia. Hole	Black	P724BK	PJ724BK	Aluminum	-
	Ivory	P724I	PJ724I	Brass	①
	White	P724W	PJ724W	Brass Plated	①
				Chrome	SCH723
				S/S 302/304	SS723
 2-Gang, 1-Single, 2.16 in. (54.9) Dia. Hole				Aluminum	-
				Brass	-
				Chrome	-
				S/S 302/304	SS702
 2-Gang, 1-Single, 2.16 in. (54.9) Dia. Hole	Black	P703BK	PJ703BK	Aluminum	-
	Ivory	P703I	PJ703I	Brass	-
	White	P703W	PJ703W	Brass Plated	-
				Chrome	-
				S/S 302/304 S/S 430	SS703 SS703L
 2-Gang, 1-Single, 2.48 in. (63.0) Dia. Hole				Aluminum	-
				Brass	-
				Chrome	-
				S/S 302/304	SS701
 2-Gang, 1-Single, 2.66 in. (67.6) Dia. Hole				Aluminum	-
				Brass	-
				Chrome	-
				S/S 302/304	SS716

Note: Thermoplastic wallplates feature pre-inserted captive screws for faster assembly in single gang configurations.

① Available as a custom wallplate, see pages N-32 to N-34. Consult custom wallplates section for additional openings and combinations.

Dimensions in Inches (mm)