






## Flush Round Single Service Metal Floor Boxes, for Use In Concrete Floors

Style	Cast Iron			Stamped Steel	
					
Catalog Numbers	<b>FB2536</b>	<b>FB2537</b>	<b>FB2546</b>	<b>FB2527</b>	<b>FB2529</b>
Cover Frame Material	Steel	Steel	Steel	Steel	Steel
Min. Depth of Pour	3.25" (82.6)	3.00" (76.2)	3.75" (95.3)	4.00" (101.6)	3.00" (76.2)
Adjustability	Fully	Fully	Fully	Fully	Fully
Before Pour External Height Adjustment	1.25" (31.8)	1.25" (31.8)	–	1.25" (31.8)	1.25" (31.8)
After Pour Internal Height Adjustment	.50" (12.7)	.50" (12.7)	.625" (15.9)	.50" (12.7)	.50" (12.7)
Cubic Inch (cm <sup>3</sup> ) Capacity	33.0 (540.8)	30.0 (491.7)	36.0 (590.0)	54.0 (884.9)	37.3 (611.2)
Dimensions – A	3.12" (79.1)	2.87" (72.8)	3.61" (91.6)	3.80" (96.4)	2.82" (71.5)
Dimensions – B	4.85" (123.2)	4.85" (123.2)	5.00" (126.9)	4.81" (122.2)	4.81" (122.2)
Dimensions – C	4.85" (123.2)	4.85" (123.2)	–	6.00" (152.4)	6.00" (152.4)
Dimensions – D	4.21" (106.8)	4.21" (106.8)	4.21" (106.8)	4.21" (106.8)	4.21" (106.8)
Threaded Hubs	(4) 1"	(4) ¾"	(4) 1"	–	–
Knockouts – Sides	–	–	–	(2) 3/4", 1", 1-1/4"	(2) ½" & (1) ¾"
Knockouts – Ends	–	–	–	(2) 3/4", 1", 1-1/4"	(1) ½" & (1) ¾"
Knockouts – Bottom	–	–	–	(2) 3/4", 1", 1-1/4"	(2) 3/4", 1", 1-1/4"
Concrete Cover Included	✓	✓	✓	✓	✓
Closure Plugs Included	✓	✓	✓	–	–
1" to 3/4" Threaded Reducer	2 Each	–	2 Each	–	–

Note: Suitable for single service applications only. UL File Number E31999. CSA File Number LR18416.

### Cover Adapter Ring, Flush Application

**Required** for tile or finished concrete applications.




### Carpet Flanges, Surface Applications


**Required** for carpet and surface applications.



### Single Service Covers†



### One Piece Brass Cover and Carpet Flange†



\*Note: brass plated aluminum

†COVER LOAD RATING; Metallic covers and flanges 2,000 lbs. with 2x safety factor, Non-metallic covers and flanges 300 lbs. Load applied through a 3 in. (76) mandrel at the center of the cover.

Dimensions in Inches (mm)