

## Flush Rectangular Non-Metallic Floor Boxes with Non-Metallic Covers, for Use In Concrete Floor

Style	1-Gang	2-Gang	3-Gang
	<p><b>PFBRG1*</b></p>	<p><b>PFBRG2</b></p>	<p><b>PFBRG3</b></p>
Min. Depth of Pour	3.00" (76.2)	3.00" (76.2)	3.00" (76.2)
Adjustability	Fully	Fully	Fully
Cubic Inch (cm <sup>3</sup> ) Capacity per Gang	14.3 cu. in. (234.3 cm <sup>3</sup> ) per 1" depth	14.3 cu. in. (234.3 cm <sup>3</sup> ) per 1" depth	14.3 cu. in. (234.3 cm <sup>3</sup> ) per 1" depth
Dimensions – A	6.00" (152.4)	6.00" (152.4)	6.00" (152.4)
Dimensions – B	3.60" (91.4)	6.80" (172.7)	10.04" (255.0)
Dimensions – C	5.47" (138.9)	5.47" (138.9)	5.47" (138.9)
Dimensions – D	6.90" (175.3)	6.90" (175.3)	6.90" (175.3)
Dimensions – E	5.41" (137.4)	8.56" (221.4)	11.75" (298.4)
Hubs	(4) 1¼"	(6) 1¼"	(8) 1¼"
Reducers	(4) 1" to ¾" and (4) 1¼" to 1"	(6) 1" to ¾" and (6) 1¼" to 1"	(8) 1" to ¾" and (8) 1¼" to 1"
Concrete Cover Included	✓	✓	✓
Closure Plugs Included	✓	✓	✓
Low Voltage Barrier**	–	(1) Removable	(2) Removable

Note: UL File Number E92074.

\*Suitable for single service applications only.

\*\*Replacement low voltage barriers, 5 pack, catalog number PFBRGLVDPK5

## Flush Rectangular Non-Metallic Covers and Flanges\*

### Required Components for Carpet Applications

Carpet Flanges				Cover with Duplex and Style Line® decorator inserts included
Number of Gangs	1-Gang	2-Gang	3-Gang	One Required per Gang
Dimensions	6.00" x 4.88"	6.00" x 8.13"	6.00" x 11.35"	4.15" x 2.97"
Black	<b>PFBRFBL1</b>	<b>PFBRFBL2</b>	<b>PFBRFBL3</b>	<b>PFBR826BLA</b>
Brown	<b>PFBRFBR1</b>	<b>PFBRFBR2</b>	<b>PFBRFBR3</b>	<b>PFBR826BRA</b>
Gray	<b>PFBRFGY1</b>	<b>PFBRFGY2</b>	<b>PFBRFGY3</b>	<b>PFBR826GYA</b>
Ivory	<b>PFBRFI1</b>	<b>PFBRFI2</b>	<b>PFBRFI3</b>	<b>PFBR826IA</b>
				<p>Cover      Duplex Insert      Style Line® Decorator Insert</p>

### Required Components for Tile Applications

Mounting Collar		Cover Frame	Cover with Duplex and Style Line® decorator inserts included
One Required per Gang		One Required per Gang	One Required per Gang
		Dim. 4.47" x 3.25"	4.15" x 2.97"
<b>PFBRMC</b>	<b>PFBRFRA</b>	<b>PFBR826GYA</b>	
		Cover	Duplex Insert      Style Line® Decorator Insert

Note: \*Flush rectangular non-metallic covers and flanges are UL listed only. Not CSA certified. COVER LOAD RATING; Non-metallic covers and flanges 300 lbs. Load applied through a 3 in. (.76) mandrel at the center of the cover.

Dimensions in Inches (mm)