

Flush Rectangular Non-Metallic Floor Boxes with Metal Covers, for Use In Concrete Floor

Style	1-Gang	2-Gang	3-Gang
	<p>PFBRG1*</p>	<p>PFBRG2</p>	<p>PFBRG3</p>
Min. Depth of Pour	3.00" (76.2)	3.00" (76.2)	3.00" (76.2)
Adjustability	Fully	Fully	Fully
Cubic Inch (cm ³) Capacity per Gang	14.3 cu. in. (234.3 cm ³) per 1" depth	14.3 cu. in. (234.3 cm ³) per 1" depth	14.3 cu. in. (234.3 cm ³) per 1" depth
Dimensions – A	6.00" (152.4)	6.00" (152.4)	6.00" (152.4)
Dimensions – B	3.60" (91.4)	6.80" (172.7)	10.04" (255.0)
Dimensions – C	5.47" (138.9)	5.47" (138.9)	5.47" (138.9)
Dimensions – D	6.90" (175.3)	6.90" (175.3)	6.90" (175.3)
Dimensions – E	5.41" (137.4)	8.56" (221.4)	11.75" (298.4)
Hubs	(4) 1 1/4"	(6) 1 1/4"	(8) 1 1/4"
Reducers	(4) 1" to 3/4" and (4) 1 1/4" to 1"	(6) 1" to 3/4" and (6) 1 1/4" to 1"	(8) 1" to 3/4" and (8) 1 1/4" to 1"
Concrete Cover Included	✓	✓	✓
Closure Plugs Included	✓	✓	✓
Low Voltage Barrier**	-	(1) Removable	(2) Removable

Note: UL File Number E92074.

*Suitable for single service applications only.

**Replacement low voltage barriers, 5 pack, catalog number PFBRGLVDPK5

Flush Rectangular Metal Covers and Flanges

Required Components for Flush Tile Applications

Adapter Collar (One required per gang)	Adapter Frame with Grounding Wire (One required per gang) Dim. 4.36" x 3.20" x 0.30"
Gray PFBRAC	Brass S5017GR Aluminum SA5017GR

Flush Rectangular Metal Covers and Flanges

Required Components for Flat Flange Applications

Adapter Collar (One required per gang)	
Gray PFBRAC	

Flat Flanges*

Flat Flange Height 0.125"

	1-Gang	2-Gang	3-Gang
Dimensions	6.00" x 4.85"	6.00" x 8.13"	6.00" x 11.34"
Brass, square edge	SB3083W	SB3084W	SB3085W
Aluminum, square edge	SA3083W	SA3084W	SA3085W
Brass, beveled edge	SB3083WB	SB3084WB	SB3085WB
Aluminum, beveled edge	SA3083WB	SA3084WB	SA3085WB

*Flange applications; square edge for carpet and recessed, beveled edge for use on hard finished surfaces

Covers – One Required per Gang[†]

	S3825	S3625	S3625TR	S3826	S2425	S2625	S2825	S3425	S3813
Brass	SA3825	SA3625	SA3625TR	SA3826	SA2425	SA2625	—	—	SA3813
Aluminum									
Dimensions	4.15" x 2.99"								
	Duplex Flap	Duplex Screw	Tamper Resistant Duplex Screw	Style Line® Decorator Opening	2 1/8" x 3/4" Combination	2 1/8" x 1" Combination	2 1/8" Single Receptacle	2 3/8" Single Receptacle	Blank

[†]COVER LOAD RATING; Metallic covers and flanges 2,000 lbs. with 2x safety factor Load applied through a 3 in. (.76) mandrel at the center of the cover.

Dimensions in Inches (mm)