



## Flush Rectangular Cast Iron Floor Boxes with Non-Metallic Covers, for Use In Concrete Floors

Style	Cast Iron					
	1-Gang Deep	2-Gang Deep	3-Gang Deep	1-Gang Shallow	2-Gang Shallow	3-Gang Shallow
						
Catalog Numbers	<b>FB4133*</b>	<b>FB4233</b>	<b>FB4333</b>	<b>FB4114*</b>	<b>FB4214</b>	<b>FB4314</b>
Cover Frame Material	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic
Min. Depth of Pour	3.50" (95.3)	3.50" (95.3)	3.50" (95.3)	2.00" (50.8)	2.00" (50.8)	2.00" (50.8)
Adjustability	Fully	Fully	Fully	Semi	Semi	Semi
Before Pour External Height Adjustment	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)
After Pour Internal Height Adjustment	.875" (22.2)	.875" (22.2)	.875" (22.2)	–	–	–
Cubic Inch (cm <sup>3</sup> ) Capacity per Gang	33.0 (540.8)	36.5 (598.2)	36.5 (598.2); 34.8 (570.3) center gang	16.0 (262.2)	16.0 (262.2)	16.0 (262.2)
Dimensions – A	3.42" (87.0)	3.40" (86.4)	3.40" (86.4)	2.03" (51.4)	2.05" (51.9)	2.06" (52.2)
Dimensions – B	4.85" (123.2)	4.91" (124.7)	4.91" (124.7)	5.66" (143.7)	5.46" (138.7)	5.46" (138.7)
Dimensions – C	4.85" (123.2)	8.13" (206.5)	11.41" (289.8)	4.38" (111.3)	7.50" (190.4)	10.71" (272.0)
Dimensions – D	4.32" (109.7)	4.32" (109.7)	4.32" (109.7)	4.32" (109.7)	4.32" (109.7)	4.32" (109.7)
Dimensions – E	3.20" (81.3)	6.42" (163.0)	9.64" (244.8)	3.20" (81.3)	6.42" (163.0)	9.64" (244.8)
Threaded Hubs	(4) 1"	(6) 1"	(8) 1"	(4) ¾"	(4) ¾"	(6) ¾"
Concrete Cover Included	✓	✓	✓	✓	✓	✓
Closure Plugs Included	✓	✓	✓	✓	✓	✓
1" to 3/4" Threaded Reducer	2 Each	4 Each	4 Each	–	–	–
Low Voltage Barrier	–	(1) Removable	(2) Removable	–	Non-Removable	Non-Removable

Note: UL File Number E92074. CSA File Number LR18416. \*Suitable for single service applications only.

## Flush Rectangular Non-Metallic Covers and Flanges\*

Required Components for Carpet Applications				Cover with Duplex and Style Line <sup>®</sup> decorator inserts included
Carpet Flanges				One Required per Gang 4.15" x 2.97"
Number of Gangs	1-Gang	2-Gang	3-Gang	
Dimensions	6.00" x 4.88"	6.00" x 8.13"	6.00" x 11.35"	
Black	<b>MFBRFBL1</b>	<b>MFBRFBL2</b>	<b>MFBRFBL3</b>	<b>PFBR826BLA</b>
Brown	<b>MFBRFBR1</b>	<b>MFBRFBR2</b>	<b>MFBRFBR3</b>	<b>PFBR826BRA</b>
Gray	<b>MFBRFGY1</b>	<b>MFBRFGY2</b>	<b>MFBRFGY3</b>	<b>PFBR826GYA</b>
Ivory	<b>MFBRFI1</b>	<b>MFBRFI2</b>	<b>MFBRFI3</b>	<b>PFBR826IA</b>



Note: \*Flush rectangular non-metallic covers and flanges are UL listed only. Not CSA certified. COVER LOAD RATING; Non-metallic covers and flanges 300 lbs. Load applied through a 3 in. (76) mandrel at the center of the cover.

Dimensions in Inches (mm)