

Flush Rectangular Stamped Steel Floor Boxes with Metal Covers, for Use In Concrete Floors

Style	Stamped Steel					
	1-Gang Deep	2-Gang Deep	3-Gang Deep	1-Gang Shallow	2-Gang Shallow	3-Gang Shallow
Catalog Numbers	FB2431*	FB2432	FB2433	FB2421*	FB2422	FB2423
Cover Frame Material	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic
Min. Depth of Pour	3.75" (95.3)	3.75" (95.3)	3.75" (95.3)	2.75" (69.9)	2.75" (69.9)	2.75" (69.9)
Adjustability	Fully	Fully	Fully	Fully	Fully	Fully
Before Pour External Height Adjustment	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)
After Pour Internal Height Adjustment	.50" (12.7)	.50" (12.7)	.50" (12.7)	.50" (12.7)	.50" (12.7)	.50" (12.7)
Cubic Inch (cm ³) Capacity per Gang	54.0 (884.9)	52.8 (865.2)	50.8 (832.5)	37.3 (611.2)	35.0 (573.5)	34.0 (557.2); 35.0 (573.5) center gang
Dimensions – A	3.73" (94.7)	3.73" (94.7)	3.73" (94.7)	2.75" (69.8)	2.75" (69.8)	2.75" (69.8)
Dimensions – B	4.81" (122.2)	4.81" (122.2)	4.81" (122.2)	4.81" (122.2)	4.81" (122.2)	4.81" (122.2)
Dimensions – C	6.00" (152.4)	9.25" (235.0)	12.50" (317.5)	6.00" (152.4)	9.25" (235.0)	12.50" (317.5)
Dimensions – D	4.32" (109.7)	4.32" (109.7)	4.32" (109.7)	4.32" (109.7)	4.32" (109.7)	4.32" (109.7)
Dimensions – E	3.20" (81.3)	6.42" (163.0)	9.64" (244.8)	3.20" (81.3)	6.42" (163.0)	9.64" (244.8)
Knockouts – Sides	(2) 3/4", 1", 1-1/4"	(4) 3/4", 1", 1-1/4"	(6) 3/4", 1", 1-1/4"	(1) 1/2" & (1) 3/4"	(8) 1/2", 3/4"	(12) 1/2", 3/4"
Knockouts – Ends	(2) 3/4", 1", 1-1/4"	(2) 3/4", 1", 1-1/4"	(2) 3/4", 1", 1-1/4"	(2) 1/2" & (1) 3/4"	(4) 1/2", 3/4"	(4) 1/2", 3/4"
Knockouts – Bottom	(2) 3/4", 1", 1-1/4"	(4) 3/4", 1", 1-1/4"	(6) 3/4", 1", 1-1/4"	(2) 3/4", 1", 1-1/4"	(4) 3/4", 1", 1-1/4"	(6) 3/4", 1", 1-1/4"
Concrete Cover Included	✓	✓	✓	✓	✓	✓
Low Voltage Barrier	–	(1) Removable	(2) Removable	–	(1) Removable	(2) Removable

Note: UL File Number E92074. CSA File Number LR18416.

*Suitable for single service applications only.

Flush Rectangular Covers Flanges

Required Components for Flush Tile or Finished Concrete Applications




Brass **S5017GR** Adapter Frame with Grounding Wire (One required per gang) Dim. 4.36" x 3.20" x 0.30"
 Aluminum **SA5017GR**



Flat Flanges*

Flat Flange Height 0.125"

Number of Gangs	1-Gang 6.00" x 4.85"	2-Gang 6.00" x 8.13"	3-Gang 6.00" x 11.34"
Brass, square edge	SB3083W	SB3084W	SB3085W
Aluminum, square edge	SA3083W	SA3084W	SA3085W
Brass, beveled edge	SB3083WB	SB3084WB	SB3085WB
Aluminum, beveled edge	SA3083WB	SA3084WB	SA3085WB



*Flange applications; square edge for carpet and recessed, beveled edge for use on hard finished surfaces

Covers – One Required per Gang[†]

	S3825 SA3825	S3625 SA3625	S3625TR SA3625TR	S3826 SA3826	S2425 SA2425	S2625 SA2625	S2825 –	S3425 –	S3813 SA3813
Brass									
Aluminum									
Dimensions 4.15" x 2.99"									
	Duplex Flap	Duplex Screw	Tamper Resistant Duplex Screw	Style Line® Decorator Opening	2 1/8" x 3/4" Combination	2 1/8" x 1" Combination	2 1/8" Single Receptacle	2 3/8" Single Receptacle	Blank

[†]COVER LOAD RATING; Metallic covers and flanges 2,000 lbs. with 2x safety factor, Non-metallic covers and flanges 300 lbs. Load applied through a 3 in. (76) mandrel at the center of the cover.