

## Metal PlugTrak® Series

Available in Standard, Isolated Ground (IG), Tamper-Resistant (TR) and USB (U) versions.



	Amp Circuits	Single Recept.	USB Ports	Receptacle Spacing (in.)	Color	
					Ivory	Gray
3 Foot	15 Single	6	—	6	<b>HBL20GB306IV</b>	<b>HBL20GB306GY</b>
	15 IG/Single	6	—	6	<b>HBL20IG306IV</b>	<b>HBL20IG306GY</b>
	15 TR/Single	6	—	6	<b>HBL20GB306IVTR</b>	<b>HBL20GB306GYTR</b>
	15 USB/Single	2	2	12	<b>HBL20GB312UIV</b>	—
	20 Single	6	—	6	<b>HBL24GB306IV</b>	<b>HBL24GB306GY</b>
	20 TR/Single	6	—	6	<b>HBL24GB306IVTR</b>	<b>HBL24GB306GYTR</b>
5 Foot	15 Single	10	—	6	<b>HBL20GB506IV</b>	<b>HBL20GB506GY</b>
	15 Single	5	—	12	<b>HBL20GB512IV</b>	<b>HBL20GB512GY</b>
	15 Two	5	—	12	<b>HBL20GBA512IV</b>	<b>HBL20GBA512GY</b>
	15 IG/Single	5	—	12	<b>HBL20IG512IV</b>	<b>HBL20IG512GY</b>
	15 TR/Single	5	—	12	<b>HBL20GB512IVTR</b>	<b>HBL20GB512GYTR</b>
	20 Single	10	—	6	<b>HBL24GB506IV</b>	<b>HBL24GB506GY</b>
	20 Single	5	—	12	<b>HBL24GB512IV</b>	<b>HBL24GB512GY</b>
	20 Two	5	—	12	<b>HBL24GBA512IV</b>	<b>HBL24GBA512GY</b>
6 Foot	15 Single	12	—	6	<b>HBL20GB606IV</b>	<b>HBL20GB606GY</b>
	15 Single	8	—	9	<b>HBL20GB609IV</b>	<b>HBL20GB609GY</b>
	15 Single	6	—	12	<b>HBL20GB612IV</b>	<b>HBL20GB612GY</b>
	15 Single	4	—	18	<b>HBL20GB618IV</b>	<b>HBL20GB618GY</b>
	15 Two	8	—	9	<b>HBL20GBA609IV</b>	<b>HBL20GBA609GY</b>
	15 Two	6	—	12	<b>HBL20GBA612IV</b>	<b>HBL20GBA612GY</b>
	15 Two	4	—	18	<b>HBL20GBA618IV</b>	<b>HBL20GBA618GY</b>
	15 IG/Single	12	—	6	<b>HBL20IG606IV</b>	<b>HBL20IG606GY</b>
	15 USB/Single	4	4	12	<b>HBL20GB612UIV</b>	—
	20 Single	12	—	6	<b>HBL24GB606IV</b>	<b>HBL24GB606GY</b>
	20 Single	6	—	12	<b>HBL24GB612IV</b>	<b>HBL24GB612GY</b>
	20 Single	4	—	18	<b>HBL24GB618IV</b>	<b>HBL24GB618GY</b>
	20 Two	6	—	12	<b>HBL24GBA612IV</b>	<b>HBL24GBA612GY</b>
	20 Two	4	—	18	<b>HBL24GBA618IV</b>	<b>HBL24GBA618GY</b>



Portable	Amp Circuits	Length (in.)	Cord Length (ft.)	Single Recept.	USB Ports	Color	
						Ivory	Gray
	15 Single	40	6	6	—	<b>HBL20C215IV</b>	<b>HBL20C215GY</b>
	15 USB/Single	40	6	4	2	<b>HBL20C215UIV</b>	—
	15 Single	64	6	10	—	<b>HBL20C315IV</b>	<b>HBL20C315GY</b>

Note: IG = Isolated Ground, TR = Tamper-Resistant and U = USB.  
 Hubbell Metal PlugTrak is supplied with two HBL2010BIV/GY blank end fittings and one HBL2001C coupling. Catalog number suffix "IV" for ivory finish and "GY" for gray finish. Outlets match raceway color. "IG" Isolated ground receptacles have orange triangles. Portable PlugTrak includes 15A circuit breaker.

Dimensions in Inches (mm)

	Description	Color	Catalog Number
Boxes	1-Gang Device Box	Ivory Gray	<b>HBL20481V</b> <b>HBL2048GY</b>
	2-Gang Device Box	Ivory Gray	<b>HBL204821V</b> <b>HBL20482GY</b>
Elbows and Tees	External Elbow	Ivory Gray	<b>HBL2018BR1V</b> <b>HBL2018BRGY</b>
	Flat Elbow	Ivory Gray	<b>HBL2011BR1V</b> <b>HBL2011BRGY</b>
	Tee	Ivory Gray	<b>HBL2015BR1V</b> <b>HBL2015BRGY</b>
End Fittings	Entrance End Fitting	Ivory Gray	<b>HBL2010A21V</b> <b>HBL2010A2GY</b>
	Large Entrance End Fitting	Ivory Gray	<b>HBL2010A31V</b> <b>HBL2010A3GY</b>
	Blank End Fitting	Ivory Gray	<b>HBL2010B1V</b> <b>HBL2010BGY</b>
	Cover Clip	Ivory Gray	<b>HBL20061V</b> <b>HBL2006GY</b>
Fittings	Supporting Clip	Steel**	<b>HBL2003SC*</b>
	Coupling	Steel**	<b>HBL2001C</b>
	Internal Corner Coupling	Steel**	<b>HBL2017TC</b>

Note: \*Support clip HBL2003SC for supporting Portable Metal PlugTrak only.  
 \*\*Galvanized Steel.  
 See pages S-10 and S-11 for additional information.