

Aluminum Raceway



Aluminum PlugTrak® Series

Available in Standard, Isolated Ground (IG), Tamper-Resistant (TR) and USB (U) versions.



USB



Tamper-Resistant

	Amp Circuits	Single Recept.	USB Ports	Receptacle Spacing (in.)	Catalog Number
3 Foot	15 Single	6	—	6	HBLALU20GB306
	15 IG/Single	6	—	6	HBLALU20IG306
	15 TR/Single	6	—	6	HBLALU20GB306TR
	15 USB/Single	2	2	12	HBLALU20GB312U
	20 Single	6	—	6	HBLALU24GB306
	20 IG/Single	6	—	6	HBLALU24IG306
	20 TR/Single	6	—	6	HBLALU24GB306TR
5 Foot	15 Single	10	—	6	HBLALU20GB506
	15 Single	5	—	12	HBLALU20GB512
	15 IG/Single	10	—	6	HBLALU20IG506
	15 TR/Single	5	—	12	HBLALU20GB512TR
	20 Single	10	—	6	HBLALU24GB506
	20 Single	5	—	12	HBLALU24GB512
	20 IG/Single	10	—	6	HBLALU24IG506
20 TR/Single	5	—	12	HBLALU24GB512TR	
6 Foot	15 Single	12	—	6	HBLALU20GB606
	15 Single	6	—	12	HBLALU20GB612
	15 Single	4	—	18	HBLALU20GB618
	15 Two	12	—	6	HBLALU20GBA606
	15 Two	6	—	12	HBLALU20GBA612
	15 Two	4	—	18	HBLALU20GBA618
	15 IG/Single	12	—	6	HBLALU20IG606
	15 USB/Single	4	4	12	HBLALU20GB612U
	20 Single	12	—	6	HBLALU24GB606
	20 Single	6	—	12	HBLALU24GB612
	20 Single	4	—	18	HBLALU24GB618
	20 Two	12	—	6	HBLALU24GBA606
	20 Two	6	—	12	HBLALU24GBA612
20 Two	4	—	18	HBLALU24GBA618	
20 IG/Single	12	—	6	HBLALU24IG606	

	Description	Catalog Number
Device Boxes	Standard 1-Gang Device Box	HBLALU2047
	Deep 1-Gang Device Box	HBLALU2044
	Standard 2-Gang Device Box	HBLALU20472
	Deep 2-Gang Device Box	HBLALU20442
	Round Box	HBLALU2038
	Elbows and Tees	External Elbow
Internal Elbow		HBLALU2017
Flat Elbow		HBLALU2011
Tee		HBLALU2015
Fittings	Cover Clip	HBLALU2006
	Supporting Clip	HBLALU2003
	Coupling	HBLALU2001
	Entrance End Fitting	HBLALU2010A
	In-Line Switch Fitting	HBLALU2040A
	Blank End Fitting	HBLALU2010B

Note: See pages S-34 and S-35 for additional information.

Note: IG = Isolated Ground, TR = Tamper-Resistant and U = USB. Hubbell Aluminum PlugTrak is supplied with two HBLALU2010B blank end fittings and one HBLALU2001 coupling.

Dimensions in Inches (mm)