


























Frame Modules and Modular Connector Fittings

1. Choose Plate Frame	Description	Color	HBL4750 Series		HBL6750 Series	
	Front loading plate will accept any modules in three unit combinations. Angled fixtures to be used in bottom opening only. Use KPIMBZOW/GY plate with modules for HBL4750 and HBL6750 Series device mounting bracket located on page S-45. See section Y for additional Hubbell iSTATION modules and datacom products.	Ivory Gray		IMF1EI IMF1GY		IMF2EI IMF2GY
<i>Note: Each gang accepts 3 module units.</i>						

2. Choose Modules	Color	Catalog Number	Catalog Number	Catalog Number	Catalog Number					
	Ivory Gray	 IMB05EI IMB05GY Blank Module .5 Unit	 IMB1EI IMB1GY Blank Module 1 Unit	 IMB15EI IMB15GY Blank Module 1.5 Unit						
	Ivory Gray	 IM1K1EI IM1K1GY Modular Flat 1 Unit	 IM2K1EI IM2K1GY Modular Flat 1 Unit	 IM1KA15EI IM1KA15GY Modular Angled 1.5 Unit	 IM2KA15EI IM2KA15GY Modular Angled 1.5 Unit					
	Ivory Gray	 IM1SCA15EI IM1SCA15GY SC 1 Duplex Angled, 1.5 Unit	 IM2SCA2EI IM2SCA2GY SC 2 Duplex Angled, 2 Unit	 IM1IA15EI IM1IA15GY Modular Recessed 1.5 Unit	 IM2IA15EI IM2IA15GY Modular Recessed 1.5 Unit					
Keystone Opening Hole size for mounting all Hubbell Jacks. <table style="display: inline-table; vertical-align: middle; margin-left: 20px;"> <tr> <td style="text-align: center;">A</td> <td rowspan="2" style="border: 1px solid black; width: 20px; height: 20px; margin: 0 auto;"></td> <td>A: .580" (14.73)</td> </tr> <tr> <td style="text-align: center;">B</td> <td>B: .760" (19.30)</td> </tr> </table>						A		A: .580" (14.73)	B	B: .760" (19.30)
A		A: .580" (14.73)								
B		B: .760" (19.30)								

Modular connectors to be used with any plate with a standard modular opening. Not recommended for use with KP plates. For KP applications use KPIMBZAL/GY bezel and appropriate Hubbell iSTATION modules located in the section Y. See section Y for additional modular connectors.

Modular Connector Fittings	Color	Catalog Number	Catalog Number	Catalog Number
	Ivory Gray	 SFFGEI SFFGGY F-Type Coupler Gold	 SFFEX SFFGX F-Type Coupler Nickel	 SFBE10 SFBG10 Blank (10 Pack)
	Ivory Gray	 SFRCRFFEI SFRCRFFGY RCA Gold Pass-through F/F Coupler Red Insulator	 SFRCWFFEI SFRCWFFGY RCA Gold Pass-through F/F Coupler White Insulator	 SFRCYFFEI SFRCYFFGY RCA Gold Pass-through F/F Coupler Yellow Insulator
	Black housing only	 SFRC110R RCA 110 Punchdown Red Insulator	 SFRC110W RCA 110 Punchdown White Insulator	 SFRC110Y RCA 110 Punchdown Yellow Insulator
	Black	 SFSV110BK S-Video 110	 SFSVBK S-Video F/F Coupler	 SFSPGBK* SFSPGR** Speaker Post Connector

Note: *Office white housing with black ring color.
**Office white housing with red ring color.

Xcelerator Modular Jacks	Color	Catalog Number	Catalog Number	Catalog Number
	Ivory Gray	 HXJ5EEI HXJ5EGY Cat. 5e, T568A, T568B, RJ45	 HXJ6EI HXJ6GY Cat. 6, T568A, T568B, RJ45	 HXJUEI HXJUGY 6 Position USOC, RJ25

Note: See section Y for additional Hubbell Xcelerator modular jacks and colors.

Dimensions in Inches (mm)