




HBL500, HBL700 and HBL750 Series

HBL500, HBL700 and HBL750 Series	Description	Color	Length	HBL500 Series	HBL700 Series	HBL750 Series
	Base and Cover Available in 5 ft. (1.5m) lengths, packed 50 ft. (15m) per carton and 10 ft. (3m) lengths, packed 100 ft. (30m) per carton. HBL5701C coupling furnished with each length.	Ivory Ivory White	5 ft. 10 ft. 10 ft.	— HBL50010IV HBL50010W A: .53" (13.46) B: .76" (19.30)	— HBL700IV HBL700W A: .67" (16.90) B: .76" (19.30)	HBL7505IV HBL75010IV HBL75010W A: .85" (21.59) B: .76" (19.30)



	Color	1-Gang	2-Gang	3-Gang	4-Gang	5-Gang	6-Gang
Standard	Ivory	HBL5748IVA	HBL57482IVA	HBL57483IVA	HBL57484IVA	HBL57485IVA	HBL57486IVA
	White	HBL5748WA A: 4.54" (115.32) B: 2.82" (71.63) C: 1.75" (44.45)	HBL57482WA A: 4.54" (115.32) B: 4.64" (117.86) C: 1.75" (44.45)	HBL57483WA A: 4.54" (115.32) B: 6.45" (163.88) C: 1.75" (44.45)	— A: 4.54" (115.32) B: 8.26" (209.91) C: 1.75" (44.45)	— A: 4.54" (115.32) B: 10.01" (255.93) C: 1.75" (44.45)	— A: 4.54" (115.32) B: 11.89" (301.96) C: 1.75" (44.45)
Shallow	Ivory	HBL5747IVA	HBL57472IVA	HBL57473IVA	—	—	—
	White	HBL5747WA A: 4.54" (115.32) B: 2.82" (71.63) C: 1.38" (35.05)	HBL57472WA A: 4.54" (115.32) B: 4.64" (117.86) C: 1.38" (35.05)	— A: 4.54" (115.32) B: 6.45" (163.88) C: 1.38" (35.05)	—	—	—
Deep	Ivory	HBL5744SIVA	HBL5744S2IVA	HBL5744S3IVA	—	—	—
	White	HBL5744SWA A: 4.54" (115.32) B: 2.82" (71.63) C: 2.25" (57.00)	HBL5744S2WA A: 4.54" (115.32) B: 4.64" (117.86) C: 2.25" (57.00)	— A: 4.54" (115.32) B: 6.45" (163.88) C: 2.25" (57.00)	—	—	—
Extra Deep	Ivory	HBL5744IVA	HBL57442IVA	HBL57443IVA	—	—	—
	White	HBL5744WA A: 4.54" (115.32) B: 2.82" (71.63) C: 2.75" (69.85)	HBL57442WA A: 4.54" (115.32) B: 4.64" (117.86) C: 2.75" (69.85)	— A: 4.54" (115.32) B: 6.45" (163.88) C: 2.75" (69.85)	—	—	—
Base Trade		2 - 1/2"	1 - 1/2", 3/4" Concentric	3 - 1/2"	4 - 1/2"	5 - 1/2"	6 - 1/2"
Size KOs			1 - Rectangular				

Note: For datacom applications, box selection is dependent on depth of connectors (jacks). See pages S-45 and S-46 for datacom product selection, or visit our site at www.hubbell-wiring.com for our Full Line Catalog and additional information.



Extension Boxes	Description	Color	1-Gang	1-Gang Deep	1-Gang Blank	2-Gang	3-Gang
	Extension Boxes To extend existing flush switch and receptacle boxes. Blank is used where it is desired to blank original outlet.	Ivory White	HBL5751IVA HBL5751WA A: 4.54" (115.32) B: 2.82" (71.63) C: 1.38" (35.05)	HBL5751AIVA HBL5751AWA A: 4.54" (115.32) B: 2.82" (71.63) C: 1.75" (44.45)	HBL5760IVA — A: 4.54" (115.32) B: 2.82" (71.63) C: 1.13" (28.70)	HBL57512IVA — A: 4.54" (115.32) B: 4.64" (117.86) C: 1.38" (35.05)	HBL57513IVA — A: 4.54" (115.32) B: 6.45" (163.88) C: 1.38" (35.05)

Dimensions in Inches (mm)