


Straight Male Cord Connectors

IP66*
SUITABILITY

Form Size 5-8



Straight Male

NPT Hub Size	Cord Diameter Inches (mm)	Form Size	Cast Aluminum	Malleable Iron
1	.88"-1.00" (22.2-25.4)	F5	SHC1046	—
	1.00"-1.13" (25.4-28.6)		SHC1047**	—
	1.13"-1.25" (28.6-31.7)		SHC1048**	—
	1.25"-1.38" (31.7-34.9)		SHC1049**	—
1¼	.75"-.88" (19.0-22.2)	F5	SHC1050	—
	.88"-1.00" (22.2-25.4)		SHC1051	—
	1.00"-1.13" (25.4-28.6)		SHC1052	SHC1052ZP
	1.13"-1.25" (28.6-31.7)		SHC1053	SHC1053ZP
	1.25"-1.38" (31.7-34.9)		SHC1054**	SHC1054ZP
1½	.75"-.88" (19.0-22.2)	F5	SHC1055	—
	.88"-1.00" (22.2-25.4)		SHC1056	—
	1.00"-1.13" (25.4-28.6)		SHC1057	SHC1057ZP
	1.13"-1.25" (28.6-31.7)		SHC1058	SHC1058ZP
	1.25"-1.38" (31.7-34.9)		SHC1059	SHC1059ZP
1½	1.38"-1.50" (34.9-38.1)	F6	SHC1061	—
	1.50"-1.63" (38.1-41.3)		SHC1062**	—
	1.63"-1.75" (41.3-44.4)		SHC1063**	—
	1.75"-1.88" (44.4-47.6)		SHC1064**	—
2	1.25"-1.38" (31.7-34.9)	F6	SHC1065	—
	1.38"-1.50" (34.9-38.1)		SHC1066	—
	1.50"-1.63" (38.1-41.3)		SHC1067	—
	1.63"-1.75" (41.3-44.4)		SHC1068	—
	1.75"-1.88" (44.4-47.6)		SHC1069	—
2	1.69"-1.81" (42.9-46.0)	F7	SHC1070	—
	1.81"-1.94" (46.0-49.2)		SHC1071	—
	1.94"-2.06" (49.2-52.4)		SHC1072**	—
	2.06"-2.19" (52.4-55.6)		SHC1073**	—
	2.19"-2.31" (55.6-58.7)		SHC1074**	—
2½	1.69"-1.81" (42.9-46.0)	F7	SHC1076	—
	1.81"-1.94" (46.0-49.2)		SHC1077	—
	1.94"-2.06" (49.2-52.4)		SHC1078	—
	2.06"-2.19" (52.4-55.6)		SHC1079	—
	2.19"-2.31" (55.6-58.7)		SHC1080	—
	2.31"-2.44" (58.7-61.9)		SHC1081**	—
3	1.69"-1.81" (42.9-46.0)	F7	SHC1086	—
	1.94"-2.06" (49.2-52.4)		SHC1088	—
	2.06"-2.19" (52.4-55.6)		SHC1089	—
	2.19"-2.31" (55.6-58.7)		SHC1090	—
	2.31"-2.44" (58.7-61.9)		SHC1091	—
3	2.44"-2.63" (61.9-66.7)	F8	SHC1092	—
	2.63"-2.81" (66.7-71.4)		SHC1093	—
	2.81"-3.00" (71.4-76.2)		SHC1094	—
	3.00"-3.25" (76.2-82.5)		SHC1095**	—

Note: See pages W-78 to W-88 for technical information and dimensional drawings.
 *IP66 Suitability when used with optional metal clad O-ring, see page W-75 for additional information.
 **Cable jacket may have to be stripped to pass through connector body.
 Locknuts sold separately. See page W-75 for additional information.