

## Low Profile NPT, PG and Metric Thread Connectors

Non-Metallic Cord Connectors.

**IP66\***  
SUITABILITY



### Low Profile NPT Cord Connectors

NPT Hub Size	Cord Diameter Inches (mm)	Black	Gray	Non-metallic Locknuts
3/8	.18"-.31" (4.6-7.9)	<b>SEC38BA*</b>	<b>SEC38GA*</b>	<b>31622002LPK50</b>
1/2	.17"-.45" (4.3-11.4)	<b>SEC50BA</b>	<b>SEC50GA</b>	<b>31622003LPK50</b>
3/4	.25"-.48" (6.35-12.19)	—	<b>SEC75RGA</b>	<b>31622007LPK50</b>
3/4	.45"-.71" (11.4-18.0)	<b>SEC75BA</b>	<b>SEC75GA</b>	<b>31622007LPK50</b>
1	.59"-1.00" (15-25.4)	<b>SEC100BA</b>	<b>SEC100GA</b>	<b>31622008LPK50</b>

Note: See pages W-78 to W-88 for technical information and dimensional drawings.  
Catalog numbers with "PK50" suffix are bulk packed 50 pieces.

### Low Profile PG<sup>A</sup> Cord Connectors

Hub Size	Cord Diameter Inches (mm)	Black	Gray	Non-metallic Locknuts
PG7	.11"-.25" (2.9-6.4)	<b>SECP7BA*</b>	<b>SECP7GA*</b>	<b>LNP7BPK100</b>
PG9	.18"-.31" (4.6-7.9)	<b>SECP9BA*</b>	<b>SECP9GA*</b>	<b>LNP9BPK100</b>
PG11	.23"-.40" (5.8-10.0)	<b>SECP11BA*</b>	<b>SECP11GA*</b>	<b>LNP11BPK100</b>
PG13.5	.17"-.47" (4.3-11.9)	<b>SECP13BA</b>	<b>SECP13GA</b>	<b>LNP13BPK100</b>
PG16	.23"-.53" (5.8-13.5)	<b>SECP16BA</b>	<b>SECP16GA</b>	<b>LNP16BPK100</b>
PG21	.45"-.71" (11.4-17.9)	<b>SECP21BA</b>	<b>SECP21GA</b>	<b>LNP21BPK100</b>
PG29	.59"-.99" (15-25.2)	<b>SECP29BA</b>	<b>SECP29GA</b>	<b>LNP29BPK25</b>
PG36	.88"-1.30" (22.2-32.0)	<b>SECP36BA</b>	<b>SECP36GA</b>	<b>LNP36BPK25</b>

### Low Profile Metric Cord Connectors

Hub Size	Cord Diameter Inches (mm)	Black	Gray	Non-metallic Locknuts
M12	.12"-.25" (2.9-6.4)	<b>SECM12B</b>	<b>SECM12G</b>	<b>LNM12BPK100</b>
M16	.11"-.31" (2.7-7.9)	<b>SECM16B</b>	<b>SECM16G</b>	<b>LNM16BPK100</b>
M20	.17"-.45" (4.3-11.4)	<b>SECM20B*</b>	<b>SECM20G*</b>	<b>LNM20BPK100</b>
M25	.49"-.71" (12.3-18.0)	<b>SECM25B*</b>	<b>SECM25G*</b>	<b>LNM25BPK100</b>
M32	.59"-.100" (15.0-25.4)	<b>SECM32B*</b>	<b>SECM32G*</b>	<b>LNM32BPK100</b>
M40	.87"-1.30" (22.0-32.0)	<b>SECM40B</b>	<b>SECM40G</b>	<b>LNM40BPK100</b>

Note: See pages W-78 to W-88 for technical information and dimensional drawings.  
Catalog numbers above with "PK100" suffix, i.e. LNP7BPK100, are bulk packed 100 per carton.  
Catalog numbers above with "PK25" suffix, i.e. LNP29BPK25, are bulk packed 25 per carton.  
\*Items indicated are UL recognized components.  
ΔPanzergerwinde.



### Low Profile Multi-Hole Cord Grip Connectors

NPT Hub Size	Cord Diameter Inches (mm)	Color	Material	Holes	Catalog Number
1/2	.205" (5.2mm)	Black	Nylon	2	<b>SEC50B252</b>
3/4	.205" (5.2mm)	Black	Nylon	3	<b>SEC75B352</b>
3/4	.205" (5.2mm)	Black	Nylon	4	<b>SEC75B452</b>
1/2	.220" (5.6mm)	Black	Nylon	3	<b>SEC50B356</b>
1	.215" (5.5mm)	Black	Nylon	9*	<b>SEC100BSMH9</b>
1 1/4	.215" (5.5mm)	Black	Nylon	13*	<b>SEC125BSMH13</b>

Note: \*Skinned bushings, field configurable.