

Accessories



Multi-Hole Cord Grip Connectors

NPT Hub Size	Cord Diameter Inches (mm)	Form Size	Material	Holes	Catalog Number
½	0.23-0.29" (5.8-7.4mm)	F2	Aluminum	2	MHC1022
¾	0.23-0.29" (5.8-7.4mm)	F3	Aluminum	4	MHC1032
½	0.23-0.29" (5.8-7.4mm)	F2	Nylon Gray	2	MHC1022CR
½	0.23-0.29" (5.8-7.4mm)	F2	Nylon Black	2	MHC2022CR
¾	0.23-0.29" (5.8-7.4mm)	F3	Nylon Gray	4	MHC1032CR
¾	0.23-0.29" (5.8-7.4mm)	F3	Nylon Black	4	MHC2032CR



Cord Connector Parts

NPT Hub Size	Cord Diameter Inches (mm)	Form Size	Bushing Catalog Number	Color Code	GOTCHA® Ring Catalog Number
¼, ⅜, ½	.062"- .125" (1.58-3.17)	F1	31518101BPK100	Green	31648035GPK100
	.125"- .187" (3.17-4.76)		31518102BPK100	Orange	31648036GPK100
	.187"- .250" (4.76-6.35)		31518103BPK100	Red	31648037GPK100
	.250"- .312" (6.35-7.93)		31518104BPK100	Black	31648038GPK100
	.312"- .375" (7.93-9.50)		31518105BPK100	White	31605010GPK100
	.375"- .437" (9.50-11.1)		31518106BPK100	Blue	31648039GPK100
½, ¾	.187"- .250" (4.76-6.35)	F2	31518110BPK100	Red	31648042GPK100
	.250"- .375" (6.35-9.50)		31518111BPK100	White	31605015GPK100
	.375"- .500" (9.50-12.7)		31518112BPK100	Blue	31648043GPK100
	.500"- .625" (12.7-15.8)		31518113BPK100	Brown	31648044GPK100
½, ¾	.375"- .500" (9.50-12.7)	F3	31518116BPK100	Blue	31648045GPK100
	.500"- .625" (12.7-15.8)		31518117BPK100	Brown	31648046GPK100
	.625"- .750" (15.8-19.0)		31518118BPK100	Yellow	31648047GPK100
	.750"- .875" (19.0-22.2)		31518119BPK100	Orchid	31648048GPK100
1	.500"- .625" (12.7-15.8)	F4	31518123BPK100	Brown	31648050GPK100
	.625"- .750" (15.8-19.0)		31518124BPK100	Yellow	31648051GPK100
	.750"- .875" (19.0-22.2)		31518125BPK100	Orchid	31648052GPK100
	.875"- 1.00" (22.2-25.4)		31518126BPK100	Gray	31648053GPK100
	1.00"- 1.125" (25.4-28.5)		31518127BPK100	Pink	31648054GPK100

Note: Catalog numbers above with "PK100" suffix, i.e. 31518101BPK100, are bulk packed 100 per carton



Locknuts and Metal Clad Sealing O-Rings

NPT Hub Size	Zinc-Plated Steel Locknuts	Non-Metallic Locknuts	Metal Clad Sealing O-Rings*
¼	—	31622001LPK50	—
⅜	—	31622002LPK50	—
½	00322001LPK50	31622003LPK50	20509001
¾	00322002LPK50	31622007LPK50	20509002
1	00322003LPK50	31622008LPK50	20509003
1¼	00322004LPK50	—	20509004
1½	00322005LPK50	—	20509005
2	00322006LPK50	—	20509006
2½	00322007LPK50	—	20509007
3	00322008LPK50	—	20509008

Note: Catalog numbers above with "PK50" suffix, i.e. 00322001LPK50, are bulk packed 50 per carton. See page W-87 for technical information and dimensional drawings.
*UL listed and CSA certified.