

Kellems® Wire Management Products

Features and Benefits

PolyTuff® I and PolyTuff® II Non-Metallic Liquidtight Conduit

All non-metallic construction ends fatigue and separation problems. They can be cut cleanly with a knife or PVC cutter so there are no jagged metal edges.



PolyTuff® I Conduit, Gray

- Rigid PVC core bonded to flexible PVC jacket
- Approved for outdoor use and direct burial
- UL Listed and CSA Certified



PolyTuff® II Tubing, Black

- PVC core with corrugated walls bonded to PVC jacket
- Handles twists, turns, bends, switchbacks and straightaways with ease
- UL Recognized and CSA Certified

PolyTuff® I Conduit

IP66
SUITABILITY



Trade Size (metric designator)	Feet (m)	Catalog Number
3/8 (12)	100 (30.5)	G1038
	1200 (365.8)	G1038R1200
1/2 (16)	100 (30.5)	G1050
	1000 (304.8)	G1050R1000
3/4 (21)	100 (30.5)	G1075
	500 (152.4)	G1075R500
1 (27)	100 (30.5)	G1100
	500 (152.4)	G1100R500
1 1/4 (35)	100 (30.5)	G1125
1 1/2 (41)	50 (15.2)	G1150
2 (53)	50 (15.2)	G1200

Note: See pages W-58 and W-59, W-90 and W-91 for approved fittings.
See pages W-92 and W-93 for technical information and dimensional drawings.



PolyTuff® II Tubing

IP66
SUITABILITY



Trade Size (metric designator)	Feet (m)	Catalog Number
1/4 (10)	100 (30.5)	B2025
3/8 (12)	100 (30.5)	B2038
	1200 (365.8)	B2038R1200
1/2 (16)	100 (30.5)	B2050
	1000 (304.8)	B2050R1000
3/4 (21)	100 (30.5)	B2075
	800 (243.8)	B2075R800
1 (27)	100 (30.5)	B2100
	500 (152.4)	B2100R500
1 1/4 (35)	100 (30.5)	B2125
1 1/2 (41)	50 (15.2)	B2150
2 (53)	50 (15.2)	B2200

Note: See page W-90 for approved fittings.
See pages W-92 and W-93 for technical information and dimensional drawings.

