

## SNAPConnect® Devices & Accessories

### Modular wiring system

Our labor-saving receptacles and switches save up to 5 minutes per device. Perfect for prefab applications. The SNAPConnect terminal can be part of the pre-assembly. The device can be snapped in during pre-assembly or during trim out. Secure and fast, these products eliminate exposed live terminals.

- Modular wiring system eliminates screw terminals and NEC® torque requirements, speeding installation and trim-out
- Clear polycarbonate terminal connector housing to inspect contacts
- Receptacles available in standard, tamper-resistant and power indicating LED versions
- Abuse resistant nylon for extra heavy use applications
- Stainless steel autoground
- Simplifies device change out for end users



### SNAPConnect® Right Angle Pigtailed Connectors for Receptacles

Description	Solid	Stranded
6 inch wire connector	<b>SNAP1RNA</b>	<b>SNAP2RNA</b>
6 inch wire with push-wire terminals	<b>SNAP1RNAM2</b>	<b>SNAP2RNAM2</b>

### Hospital Grade SNAPConnect® Extra Heavy Duty Duplex Receptacles

Description	Style	Color	15A 125A	20A 125V
Standard	Duplex StyleLine Decorator	White	<b>SNAP8200WNA</b> <b>SNAP2172WNA</b>	<b>SNAP8300WNA</b> <b>SNAP2182WNA</b>
Standard with Finder Groove	Duplex	White	<b>SNAP8200WA</b>	<b>SNAP8300WA</b>
Tamper-Resistant	Duplex StyleLine Decorator	White	<b>SNAP8200WTRA</b> <b>SNAP2172WTRA</b>	<b>SNAP8300WTRA</b> <b>SNAP2182WTRA</b>
Tamper-Resistant with Split Circuit	Duplex StyleLine Decorator	White	<b>SNAP8200WSCTRA</b> <b>SNAP2172WSCTRA</b>	<b>SNAP8300WSCTRA</b> <b>SNAP2182WSCTRA</b>
Standard with Power Indicating (LED)	Duplex StyleLine Decorator	White	<b>SNAP8200WL</b> <b>SNAP2172WL</b>	<b>SNAP8300WL</b> <b>SNAP2182WL</b>
Tamper-Resistant with Power Indicating (LED)	Duplex StyleLine Decorator	White	<b>SNAP8200WLTRA</b> <b>SNAP2172WLTRA</b>	<b>SNAP8300WLTRA</b> <b>SNAP2182WLTRA</b>

### Specification Grade SNAPConnect® Extra Heavy Duty Duplex Receptacles

Description	Style	Color	15A 125A	20A 125V
Standard	Duplex StyleLine Decorator	White	<b>SNAP5262WNA</b> <b>SNAP2152WNA</b>	<b>SNAP5362WNA</b> <b>SNAP2162WNA</b>
Standard with Finder Groove	Duplex	White	<b>SNAP5262WA</b>	<b>SNAP5362WA</b>
Tamper-Resistant	Duplex StyleLine Decorator	White	<b>SNAP5262WTRA</b> <b>SNAP2152WTRA</b>	<b>SNAP5362WTRA</b> <b>SNAP2162WTRA</b>
Tamper-Resistant with Split Circuit	Duplex StyleLine Decorator	White	<b>SNAP5262WSCTRA</b> <b>SNAP2152WSCTRA</b>	<b>SNAP5362WSCTRA</b> <b>SNAP2162WSCTRA</b>
Standard with Power Indicating (LED)	Duplex StyleLine Decorator	White	<b>SNAP5262WL</b> <b>SNAP2152WL</b>	<b>SNAP5362WL</b> <b>SNAP2162WL</b>
Tamper-Resistant with Power Indicating (LED)	Duplex StyleLine Decorator	White	<b>SNAP5262WLTRA</b> <b>SNAP2152WLTRA</b>	<b>SNAP5362WLTRA</b> <b>SNAP2162WLTRA</b>



Dimensions in Inches (mm)