

## Features and Benefits

### AV In-Wall Boxes

Power, data, interfaces and more will mount discretely behind the flat screen. Covers two piece are available in white or black. Supplied with mounting screws for wood or steel stud mounting, grounding screws, tie wraps, and a rubber grommet. One of the single gang knockouts has a 1"x2" oblong internal knockout and can be used with the supplied grommets. The flush box installation allows flat panel displays and interactive "smart" boards to sit flush against walls with no dangling cords.

- Low voltage conduit feed-thru for connectorized cables with 1", 1-1/2" and 2" Knockouts
- 3/4" extension available for concrete block walls
- Two-piece paintable cover allows for better cable management
- Boxes Conforms to UL 62368-1:2019 Ed.3, Certified to CSAC22.2#62368-1:2019 Ed.3



HRWB25WHT with 2 Inch Low Voltage Feed-Through



HRWB25WHT



HRWB25WHT with HRW25BE075

### Wall Boxes

Description	Height	Width	Depth	Cover Color	Catalog Number
Recessed 5-Gang wall box w/ 2" feed-thru	7.24" (183.8)	14.25" (362.0)	4.00" (141.6)	White	<b>HRWB25WHT</b>
<b>HRWB25WHT</b> replacement covers	8.34" (211.7)	15.50" (393.7)	0.16" (4.0)	White	<b>HRWB25WHTRC</b>
Recessed 5-Gang wall box w/ 2" feed-thru	7.24" (183.8)	14.25" (362.0)	4.00" (141.6)	Black	<b>HRWB25BLK</b>
<b>HRWB25BLK</b> replacement covers	8.34" (211.7)	15.50" (393.7)	0.16" (4.0)	Black	<b>HRWB25BLKRC</b>
<b>HRWB25</b> series wall box 3/4" extension	7.47" (189.7)	14.50" (368.3)	0.75" (19.1)	Steel	<b>HRWB25BE075</b>



IFP16W



NSOKPS



IMF1W



HXJ6W



SFHC14W

### Power Kits

Description	Color	Catalog Number
Standard power kit.	White	<b>NSOKPTR</b>
Surge protected power kit.	White	<b>NSOKPS</b>

### AV Connectors and Plates

Description	Color	Catalog Number
1-Gang 6-Port Plate.	White	<b>IFP16W</b>
1-Gang Hubbell iSTATION Plate	White	<b>IMF1W</b>
Category 6 Jack	White	<b>HXJ6W</b>
HDMI Feed-Thru	White	<b>SFHC14W</b>

Dimensions in Inches (mm)