

## 4<sup>1</sup>/<sub>16</sub>" Square boxes

### Featuring STAB-IT<sup>®</sup> connectors

Integrated into the box, our exclusive connectors are field proven to terminate MC cable up to 3 times faster than traditional cable clamps. It's easy: remove the pry-out, prep the cable, insert cable, done!

These welded large boxes provide more room for wiring and include connectors for three or six cables, plus a knockout on the same side as the connectors. Available mounting brackets and cable management offer the first means of support.

- 3-cable STAB-IT connectors install 3 times faster than traditional connectors
- Designed for quick installation of flex, MC, MCI, MCI-A, MC-PCS, AC, and HCF Cable
- HBL252MSCM & HBL252MS include far-side support on back
- Includes ground wires, box mounting brackets and cable clamps
- Easier installation for labor savings



### Boxes

Boxes are 4<sup>1</sup>/<sub>16</sub>" square, 2<sup>1</sup>/<sub>16</sub>" deep. They are constructed with welded steel and have raised grounds. The boxes have 42 in.<sup>3</sup> capacity.

Box Description	Side Knock Outs		Back Knock Outs		
	TKO	Cable Pry-outs	Concentric	TKO	Catalog Number
Standard	(12) 1/2"-3/4"		(1) 1/2"	(3) 1/2"-3/4"	<b>HBL257*</b>
(1) STAB-IT Connector and 8" Solid #12 Ground Pigtail	(10) 1/2"-3/4"	3	(1) 1/2"	(1) 1/2"-3/4"	<b>HBL252S</b>
(1) STAB-IT Connector, 8" Solid #12 Ground Pigtail and (1) Cable Management Clamp	(10) 1/2"-3/4"	3	(1) 1/2"	(1) 1/2"-3/4"	<b>HBL252SCM</b>
(1) STAB-IT Connector, 8" Solid #12 Ground Pigtail and (1) Mounting Bracket	(10) 1/2"-3/4"	3	(1) 1/2"	(1) 1/2"-3/4"	<b>HBL252MS</b>
(1) STAB-IT Connector, 8" Solid #12 Ground Pigtail, (2) Mounting Brackets and (1) Cable Management Clamp	(10) 1/2"-3/4" (1) 3/4"-1"	3	(1) 1/2"	(1) 1/2"-3/4"	<b>HBL252MSCM</b>
(2) STAB-IT Connectors and 8" Solid #12 Ground Pigtail	(8) 1/2"-3/4"	6	(1) 1/2"		<b>HBL254S</b>
(2) STAB-IT Connectors, 8" Solid #12 Ground Pigtail, and (2) Cable Management Clamps	(8) 1/2"-3/4"	6	(1) 1/2"		<b>HBL254SCM</b>

\*UL Listed Only



Dimensions in Inches (mm)