

## Accessories

### Features

netSELECT® Accessories enhance system capabilities. Volume controls expand home audio applications. Cabinet mounted receptacle kits provide convenience power to the enclosure.

- Audio controls available in slide or rotary
- Receptacles available in surge and standard kits



**NSOSAVC**



**NSORAVC**



**NSOKPS**



**FLOCK1**



**NSOFSB**



**FSPFP6X**



**FSPHD6X**

### Accessories

Description	Color	Catalog Number
Slide Audio Volume Controller, Decorator Styling, Power handling - 70W RMS@20° C. Impedance matching for up to 8 pairs of speakers. Includes both ivory and white slides and frames.	Ivory/White	<b>NSOSAVC</b>
Rotary Audio Volume Controller Power handling - 70W RMS@20° C. Impedance matching for up to 8 pairs of speakers. Includes both ivory and white knobs and frames.	Ivory/White	<b>NSORAVC</b>
Standard Power Kit, Includes tamper-resistant duplex receptacle 15A 125V NEMA 5-15R, electrical steel box and wallplate.		<b>NSOKPTR</b>
Surge Suppression Power Kit, Includes surge receptacle 15A 125V NEMA 5-15R, 240 Joules/15,000A protection per mode, electrical steel box and wallplate.		<b>NSOKPS</b>
Chromed Steel Lock Kit, Includes two keys. Eliminates unwanted tampering.		<b>FLOCK1</b>
Panel Bracket Adapter, For use with Adapter Panels shown below, and FSP series modules. Snap mounts into structured cabling enclosures.		<b>NSOFSB</b>
F-Connector Adapter Panel, with Six Populated Coaxial Connectors.		<b>FSPFP6X</b>
Jacks Adapter Panel, with Six Blank Openings for jacks and snap fits.		<b>FSPHD6X</b>