

## Digital AV Connections



### RJ-45 Couplers

Female to female couplers

Housing Color	Category 6, Pass-Thru	Category 5e, Pass-Thru	Category 5e, Cross Over 10/100BASE-T	Category 6, Shielded Pass-Thru
Black	<b>SFC6BK</b>	<b>SFC5EBK</b>	-	Lead free tinned shield
Gray	-	-	<b>SF5ECOY</b>	<b>SFSC6</b>
White	<b>SFC6W</b>	<b>SFC5EW</b>	-	



### USB Connectors

Pass-thru, female to female couplers

Housing Color	USB 3.0, A to A	USB 3.0, A to B	USB 2.0, A to A	USB 2.0, A to B
Black	<b>SFUSBAA3BK</b>	<b>SFUSBAB3BK</b>	-	-
Blue	-	-	<b>SFUSBAAB</b>	<b>SFUSBABB</b>
Office White	-	-	<b>SFUSBAAOW</b>	<b>SFUSBABOW</b>
White	-	-	<b>SFUSBAAW</b>	<b>SFUSBABW</b>



### HDMI Connectors for IMB and ISFB Series

Color	HDMI Feed-Thru	HDMI Feed-Thru Coupler	HDMI Feed-Thru 3-Inch Tail
Black	<b>SFHC14BK</b>	<b>HDMIC14</b>	<b>HDMIT14</b>
White	<b>SFHC14W</b>	-	-



### HDMI Decorator Frames

Color	1-Port	2-Port
Black	<b>NS801BK</b>	<b>NS802BK</b>
Gray	<b>NS801GY</b>	<b>NS802GY</b>
Ivory	<b>NS801I</b>	<b>NS802I</b>
Light Almond	<b>NS801LA</b>	<b>NS802LA</b>
White	<b>NS801W</b>	<b>NS802W</b>



### HDMI Non-Active Horizontal Patch Cords

Black, non-plenum, #24 AWG, HDMI 4K

Length (ft)	HDMI Device Patch Cords
3	<b>HDPC03BK</b>
6	<b>HDPC06BK</b>



Length (ft)	In-Wall Cords (Male w/ Screw to Male w/ Screw)
10	<b>HDH10BK</b>
15	<b>HDH15BK</b>
20	<b>HDH20BK</b>
25	<b>HDH25BK</b>
30	<b>HDH30BK</b>