

Combination Switches/Devices

Features

Mini-toggles provide for multiple switches in a compact single gang. Maximize control while maintaining function and appearance.

- Low profile, less than 1 inch
- Self-grounding feature is standard
- Combination devices provide compact switches in a single-gang opening
- Smooth toggle action
- Multiple-drive Slot/Phillips/Robertson head screws
- Hi-visibility yellow base for easy installation
- Operating temperature: -20°C to 60°C
- UL Listed, CSA Certified



RC1081

Combination Toggle Switches/Devices

Description	Two (2) Single Pole Switches	Single Pole Switch, Tamper-Resistant, 2 Pole, 3 Wire, Receptacle	Single Pole Switch, 2 Pole, 3 Wire, Receptacle	Single Pole Switch, Pilot Light, Clear Lens, Amber Neon Bulb*
Termination	Self-Grounding, Side Wire	Self-Grounding, Side Wire	Self-Grounding, Side Wire	Self-Grounding, Side Wire
Rating	15A 120V AC	15A 120V (switch) 15A 125V (recept.) NEMA 5-15R	15A 120V (switch) 15A 125V (recept.) NEMA 5-15R	15A 120V AC
Color				
	Brown RC101 Ivory RC101I Light Almond RC101LA White RC101W	Brown RC108TR Ivory RC108ITR Light Almond RC108LATR White RC108WTR	Brown RC108 Ivory RC108I Light Almond RC108LA White RC108W	Brown RC109 Ivory RC109I Light Almond RC109LA White RC109W

Note: See page Tech-10 for Tamper-Resistant description.
*Neutral required for pilot light, see page Z-4 for wiring diagram.

Combination Toggle Switches/Devices

Description	Single Pole and Three Way Switch	Two (2) Three Way Switches	Three Way Switch, Tamper-Resistant, 2 Pole, 3 Wire, Receptacle	Three Way Switch, 2 Pole, 3 Wire, Receptacle	Three Way Switch, Pilot Light, Clear Lens, Amber Neon Bulb*
Termination	Self-Grounding, Side Wire	Self-Grounding, Side Wire	Self-Grounding, Side Wire	Self-Grounding, Side Wire	Self-Grounding, Side Wire
Rating	15A 120V AC	15A 120V AC	15A 120V (switch) 15A 125V (recept.) NEMA 5-15R	15A 120V (switch) 15A 125V (recept.) NEMA 5-15R	15A 120V AC
Color					
	Brown RC103 Ivory RC103I Light Almond RC103LA White RC103W	Brown RC303 Ivory RC303I Light Almond RC303LA White RC303W	Brown RC308TR Ivory RC308ITR Light Almond RC308LATR White RC308WTR	Brown RC308 Ivory RC308I — White RC308W	Brown RC309 Ivory RC309I — White RC309W

Note: See page Tech-10 for Tamper-Resistant description.
*Neutral required for pilot light, see page Z-4 for wiring diagram.

Dimensions in Inches (mm)