


XClamp and Duplex Receptacles

Features

- Eliminates the need to loop the wire
- External back-wire clamp for fast and easy installation of 15A & 20A branch circuits in residential applications
- Compression plates maximize holding power to provide a stronger, more secure connection
- Terminate up to 8 wires
- Accommodates #12 & #14 AWG wire
- Break-off tabs for switched receptacle applications
- Tamper-resistant shutter complies with NEC®

Best Solution for Residential 15A & 20A Branch Circuit Wiring

Fast and Secure



- 1** Strip the wire
- 2** Insert the wire
- 3** Clamp the connection



RR15SWTRX

XClamp Duplex Receptacles

Description	Color	Catalog Number
Tamper-Resistant, 15A 125V, 2 Pole, 3 Wire Grounding, 20A Circuit Rated	Ivory Light Almond White	RR15SITRX RR15SLATRX RR15SWTRX

Listings

UL listed to UL498 File No. E2186
 Certified to CSA C22.2, No. 42
 NEMA® WD-6 Compliant

Duplex Receptacles, 2 Pole, 3 Wire



RR15W

RR15QW

Description	Tamper-Resistant, Quick Thread	Standard	Weather and Tamper-Resistant	Tamper-Resistant
	Termination	Self-Grounding, Push and Side Wire	Grounding, Push and Side Wire	Self-Grounding, Push and Side Wire
Rating	15A 125V NEMA 5-15R	15A 125V NEMA 5-15R	15A 125V NEMA 5-15R	15A 125V NEMA 5-15R
Black	—	RR15BK	RR15SBKWRTR	RR15SBKTR
Brown	—	RR15	RR15SWRTR	RR15STR
Gray	—	—	RR15SGYWRTR	—
Ivory	RR15QITR	RR15I	RR15SIWRTR	RR15SITR
Light Almond	RR15QLATR	RR15LA	RR15SLAWRTR	RR15SLATR
White	RR15QWTR	RR15W	RR15SWWRTR	RR15SWTR

NEC® is a registered trademark of the National Fire Protection Association (NFPA).