

## Special Use Products



**RW15400GY**

### Weather Resistant Recessed Receptacle with While-In Use Cover

| Description  | Housing Color | Horizontal Mount | Vertical Mount   |
|--|---------------|------------------|------------------|
| Weather and tamper-resistant duplex receptacle with clear while-in-use cover, 15A 125V | Gray          | <b>RW15300GY</b> | <b>RW15400GY</b> |
|  | White         | <b>RW15300W</b>  | <b>RW15400W</b>  |
|  | Brown         | <b>RW15300BR</b> | <b>RW15400BR</b> |



**RR151CHWTR**



### Special Use Products



| Description  | Color           | Tamper-Resistant   | Tamper-Resistant   |
|--|-----------------|--------------------|--------------------|
| Clock Hanger/Recessed Single Receptacle, Tamper-Resistant, 2 pole, 3 wire, grounding, side wire terminations   | Brass           | <b>RR151CHBSTR</b> | <b>RR201CHBSTR</b> |
|  | Stainless Steel | <b>RR151CHSSTR</b> | <b>RR201CHSSTR</b> |
|  | Ivory (Nylon)   | <b>RR151CHITR</b>  | <b>RR201CHITR</b>  |
|  | White (Nylon)   | <b>RR151CHWTR</b>  | <b>RR201CHWTR</b>  |
| Recessed Duplex Receptacle, Tamper-Resistant, 2 pole, 3 wire, grounding, side wire terminations  | Ivory           | <b>RR1510I</b>     | —                  |
|  | Light Almond    | <b>RR1510LA</b>    | —                  |
|  | White           | <b>RR1510W</b>     | —                  |
| JLOAD® Multimedia Outlet, Provides power, Cat. 5e and coaxial in a single gang box. Requires RJ600 Box. Includes decorator frame, one Cat. 5e, one F-connector and one power receptacle 125V with voltage dividers*. | Black           | <b>RJ650BKTR</b>   | <b>RJ620BKTR</b>   |
|  | Gray            | <b>RJ650GYTR</b>   | <b>RJ620GYTR</b>   |
|  | Ivory           | <b>RJ650ITR</b>    | <b>RJ620ITR</b>    |
|  | Light Almond    | <b>RJ650LATR</b>   | <b>RJ620LATR</b>   |
|  | White           | <b>RJ650WTR</b>    | <b>RJ620WTR</b>    |
| JLOAD® Multimedia Outlet, Includes decorator frame with two open ports for custom configuration and one power receptacle 125V with voltage dividers*.  | Black           | <b>RJ65BKTR</b>    | <b>RJ62BKTR</b>    |
|  | Gray            | <b>RJ65GYTR</b>    | <b>RJ62GYTR</b>    |
|  | Ivory           | <b>RJ65ITR</b>     | <b>RJ62ITR</b>     |
|  | Light Almond    | <b>RJ65LATR</b>    | <b>RJ62LATR</b>    |
|  | White           | <b>RJ65WTR</b>     | <b>RJ62WTR</b>     |
| JLOAD® Multimedia Box, 3 inches deep with seven ½-inch knockouts, non-metallic sheathed cable clamps on each side. Screw in mounting to stud.  | Steel           | <b>RJ600</b>       | <b>RJ600</b>       |



**RR1510W**

**RJ650BKTR**



**Dividers**



**RJ600**

Note: \*Dividers provided for use with the RJ600, RF515 series and RU200 series boxes. RF408 required for use with the RF400 series floor boxes.

See page Z-10 for snap fit inserts.

See pages Z-21 to Z-26 for floor boxes and under cabinet power distribution options.

See page Tech-10 for Tamper-Resistant description.



**RS100W**



**RS101W**

### In-Line Cord Switches

| Description | Mini For Use with Flat Lamp Cord | Heavy Duty                        |
|-------------|----------------------------------|-----------------------------------|
| Rating      | 6A 125V AC                       | 6A 125V AC, 1/6 HP                |
| Wire        | #18 AWG<br>SPT 1 and SPT 2       | #18 to #16 AWG<br>SPT 1 and SPT 2 |
| Ivory       | —                                | <b>RS101I</b>                     |
| White       | <b>RS100W</b>                    | <b>RS101W</b>                     |

Dimensions in Inches (mm)