tradeSELECT® Products

Dimmers and Fan Speed Controls

Features

Standard rocker, toggle, slide and rotary styles for any interior design.

- Optimum CFL and LED Control
- Low End Adjustment for Fine Tuning
- Decorator and Traditional Toggle Styling Available
- No Neutral Required

CFL/LED Dimmers

Description	Rocker Dimmer	Toggle Dimmer
Rating	CFL/LED 150W Incadescent/ Halogen 600W 120V AC, 60Hz	CFL/LED 150W Incadescent/ Halogen 600W 120V AC, 6 0Hz
Termination	Single Pole/Three Way	Single Pole/Three Way
lvory Light Almond White	RDVCL153PI RDVCL153PLA RDVCL153PW	RAYCL153PI RAYCL153PLA RAYCL153PW

Rotary Incandescent Dimmers

Description	ON/OFF Dimmer	Push ON/OFF Dimmer Ivory and White Knobs Provided	Push ON/OFF Dimmer Ivory and White Knobs Provided
Termination	Single Pole	Single Pole	Three Way
Rating	600W 120V AC	600W 120V AC	600W 120V AC
lvory	RD600RI	_	_
White	RD600RW	-	_
lvory/White	_	RD600PDK	RD603PDK

Slide Incandescent Dimmers


Description	Slide to OFF	Preset with ON/OFF Switch	Preset with ON/OFF Switch
Termination	Single Pole	Single Pole	Three Way
Rating	600W 120V AC	600W 120V AC	600W 120V AC
lvory Light Almond White	RS600I RS600LA RS600W	RS600PI RS600PLA RS600PW	RS603PI RS603PLA RS603PW

Fan Speed Controls, 3 Speed

Description	Toggle	Rotary ON/OFF Knobs Provided
Termination	Single Pole/Three Way	Single Pole
Rating	1.5A 120V AC	1.5A 120V AC
lvory	RAYFSQFI	_
Light Almond	RAYFSQFLA	_
White	RAYFSQFW	_
lvory/White	-	RFSQ2FDK

Fan Speed Controls, 3 Speed

Description	Rocker Slide Adjustment	Slide Control Slide to OFF
Termination	Single Pole/Three Way	Single Pole
Rating	1.5A 120V AC	1.5A 120V AC
lvory Light Almond White	RDVFSQFI RDVFSQFLA RDVFSQFW	RSFSQFI RSFSQFLA RSFSQFW



Replacement Knobs

R28032406

R28032401

Replacement Knobs







RAYCL153PW

Replacement Knobs

2 Piece Kit Replacement Knobs

RRKDK

_



RS600PW



RFSQ2FDK



RSFSQFW





RSKW

(h) (h



R28032406

RSKI