




Slide and Rotary Control Dimmers




AS103
1000W Dimmer
Fits Single-Gang Wall Boxes



AS203
2000W Dimmer
Fits Single-Gang Wall Boxes



AR101
1000W Dimmer
Fits Single-Gang Wall Boxes



AR201
2000W Dimmer
Fits Single-Gang Wall Boxes

Architectural Grade, Incandescent Preset Slide Control Dimmers

Description	Color	Rating	Catalog Number
Single pole/three way - preset.	White	1000W, 120V AC, 60Hz	AS103
Single pole/three way - preset.	White	2000W, 120V AC, 60Hz	AS203

Accessories

Description	Color	Catalog Number
Small wallplate kit for 600W and 1000W models. Includes non-metallic trimplate and slide.	Ivory White	AS11 AS1W
Large wallplate kit for 1500W and 2000W models. Includes non-metallic trimplate and slide.	Ivory White	AS21 AS2W

Note: The dimmers listed above can be wired for single pole or three way applications.
See page D-19 for ganging and derating.

Architectural Grade, Incandescent Rotary Control Dimmers

Description	Color	Rating	Catalog Number
Single pole - push ON/OFF.	Beige	1000W, 120V AC, 60Hz	AR101
Three way - push ON/OFF.	Beige		AR103
Single pole, rotary ON/OFF.	Beige	2000W, 120V AC, 60Hz	AR201

Accessories

Description	Color	Catalog Number
Small wallplate kit for 600W and 1000W models. Includes non-metallic trimplate and knob.	Beige White	AR1BE AR1W
Large wallplate kit for 1500W and 2000W models. Includes non-metallic trimplate and knob.	Beige White	AR2BE AR2W

Note: See page D-19 for ganging and derating.