

SystemOne Fully Adjustable 4 inch Recessed Floor Boxes and Covers, for Use In Concrete Floors

Floor Box Covers

The 4 inch recessed cover is available in a number of durable, yet beautiful finishes to match any décor. The flange height of 0.15 inch is ADA compliant and suitable for use on any floor finish. All covers are UL 514A listed and meet UL Scrubwater requirements.

Features

- Flange diameter is 5.5 inches
- Flange thickness is 0.15 inches thick and complies with ADA requirements
- Cover load rating is 1,000 lbs. with 2x safety factor* for a static load applied through a 3 inch mandrel
- Available in six finishes
 - Satin nickel, antique bronze and brushed brass are plated finishes
 - Brushed aluminum is the base material brushed and lacquered
 - Black and gray finishes are powder coat



Device Mounting Plates

Description / Catalog Number	Sub-plate	Description / Catalog Number	Sub-plate	Description / Catalog Number	Sub-plate
2X2 Sub-plate with (1) decorator device opening and (2) keystone jack openings S1R4SP2X2STYLE		(1) Style Line® decorator device opening for power or datacom applications S1R4SPSTYLE		2X2 Sub-plate with (1) decorator device opening and (2) Ortronics® TracJack® openings S1R4SP2X2STYLETJ	
2X2 Sub-plate with (1) duplex device opening and (2) keystone jack openings S1R4SP2X2DUPLEX		(1) Duplex device opening for power or datacom applications S1R4SPDUPLEX		2X2 Sub-plate with (1) duplex device opening and (2) Ortronics® TracJack® openings S1R4SP2X2DUPLEXTJ	
(4) Single 20A receptacles. Can be wired as single or two circuit with isolated ground capability, 12 inch wire leads Includes ⚡ stickers. S1R4SPQUAD		(1) 1.60 inch opening for 20 or 30A Twist-Lock® receptacle S1R4SPTWIST		(1) 1.40 inch opening for simplex receptacle S1R4SPSIMPLEX	

Architectural Cover Finishes

Finish	Recessed Activation	Furniture Feed Activation
Brushed Aluminum	CFBS1R4CVRALU	S1R4FFCVRALU
Black Powder Coat	CFBS1R4CVRBLK	S1R4FFCVRBLK
Plated Brushed Brass	CFBS1R4CVRBRS	S1R4FFCVRBRS
Plated Antique Bronze	CFBS1R4CVRBRZ	S1R4FFCVRBRZ
Gray Powder Coat Plated	CFBS1R4CVRGRY	S1R4FFCVRGRY
Plated Satin Nickel	CFBS1R4CVRNKL	S1R4FFCVRNKL

Note: *Load applied through a 3 in. (76mm) mandrel in center of the cover.



Accessories and Replacement Parts

Description	Catalog Number
Allows the conduit connections for the low voltage portion of the CFBS1R4SFB and CFBS1R4SFBCR to be increased to 2 inch capacity. The offset design helps to minimize conduit float during the concrete pour.	CFBHUB2
Set of conduit reducing adapters for use with the CFBS1R4PFB. Includes two each 1, 3/4 and 1/2 inch of the following adapters to reducing to the corresponding conduit diameter. 1 1/2, 1 1/4 and 1 inch	CFBADAPT125 CFBADAPT200
Replacement low voltage partition for use in all four CFBS1R4 series floor boxes.	CFBS1R4DIV
Replacement ground bracket for use in all four CFBS1R4 series floor boxes.	CFBS1R4GND
Replacement pre-pour concrete yellow cover for use with all four of the CFBS1R4 series floor boxes.	CFBS1R4COVER
Abandonment plate, black finish, for all CFBS1R4 series floor boxes.	S1R4CFBADMTBK
Pre-pour PVC stand increases CFBS1R4PFB box height 2.5 in. to 4.0 in. within the concrete pour.	PFBSTAND



TracJack®, Series II® and Ortronics® are registered trademarks of Ortronics/Legrand.