

Network Wiring and netSELECT® Products

AV 110 Everywhere™ Analog AV Over UTP

Tamper-Resistant Receptacle with 5V DC Power Output

Description	Color	Catalog Number
USB charger	Black	AVPS15BK
TR receptacle,	Ivory	AVPS15I
(1) USB port 3A,	Gray	AVPS15GY
switched 5V DC output,	Office White	AVPS15LA
15A, 125V AC	White	AVPS15W
decorator duplex		



USB 2.0 High Speed 110 Extenders, 100ft

Description	Color	1.5 Unit Module
4-pair UTP cable	Black	IMU11015BK
installation, up to	Ivory	IMU11015EI
100ft (305m)	Gray	IMU11015GY
	Office White	IMU11015OW
	White	IMU11015W

Note: Product consists of send and receive pair.



HDMI 1080P 110 UTP Extenders

(2) 4-pair UTP cable installation, 5V DC, up to 147ft (45m)

Color	Decorator	2 Unit Module
Black	ISFH110BK	IMH110ST2BK
Ivory	ISFH110EI	IMH110ST2EI
Gray	ISFH110GY	IMH110ST2GY
Office White	ISFH110OW	IMH110ST2OW
White	ISFH110W	IMH110ST2W

Note: Product consists of send and receive pair.



VGA and 3.5mm HD AV Extender

Extend up to 75ft (23m) over two 4-pair UTP cables, 1.5 unit

Color	Catalog Number
Black	IM15311015BK
Gray	IM15311015GY
Ivory	IM15311015EI
Office White	IM15311015OW
White	IM15311015W

Note: Product consists of send and receive pair.



RCA Component with Audio 110 Audio/Video Modules

Extend up to 75ft (23m) over (2) 4-pair UTP cables, 1.5 unit

Color	RCA Component Video, Left/Right Audio	RCA Component Video, 3.5mm Audio
Black	IMCAR11015BK	IMC3511015BK
Gray	IMCAR11015GY	IMC3511015GY
Ivory	IMCAR11015EI	IMC3511015EI
Office White	IMCAR11015OW	IMC3511015OW
White	IMCAR11015W	IMC3511015W



RCA 110 Audio/Video Modules

Extend up to 100ft (30.5m) over (1) 4-pair UTP cables, 1 unit

Color	75ft (23m) max.	100ft (30.5m) max.	
	RCA Component Video, HD	RCA Composite Video, Left/Right Audio	RCA Left/Right Audio
Black	IMCR1101BK	IMR1101BK	IMAR1101BK
Gray	IMCR1101GY	IMR1101GY	IMAR1101GY
Ivory	IMCR1101EI	IMR1101EI	IMAR1101EI
Office White	IMCR1101OW	IMR1101OW	IMAR1101OW
White	IMCR1101W	IMR1101W	IMAR1101W