

Mini-Concealed Recessed Emergency Luminaire

FEATURES

- Concealed recessed emergency luminaire for architectural applications
- Lamp-head assembly made from die-cast zinc, back-box of 20 gauge steel
- 25 Watt MR-11 halogen lamps
- Maintenance free battery with fully automatic charger
- Wall or Ceiling Mounting with hanger bar kit included
- Multiple unit spacing up to 85'
- Self-Test and Self-Diagnostics included
- Temperature Range: 16 °C - 32 °C (60 °F - 90 °F)
- UL 924 Listed



EMERGENCY LIGHTING

ORDERING INFORMATION

CLM				-	
MODEL	CAPACITY	BATTERY TYPE	LAMP WATTAGE	OPTIONS	
	50 50 Watts	Blank Lead-Calcium N Nickel-Cadmium	H25 25 Watt Halogen	CP Chicago Plenum Rated	XK Less Rough-in Kit ¹

¹To order rough-in kit only for early installation, add -XK option suffix to CLM model and CLMRK or CPCLMRK accessory separately

ACCESSORIES

MODEL	DESCRIPTION
CLRT	Remote Testing Transmitter for 30 sec. or 90 min. testing
CLMRK	Rough-in Kit ¹
CPCLMRK	Chicago Plenum Rough-in Kit ¹

ELECTRONICS

- 120/277VAC input with test switch and LED AC-on bi-color indicator light
- Low voltage disconnect protection
- AC lockout protection
- Self-test and self-diagnostics
- Brownout protection
- 15 Minute time delay re-transfer

