

SLS Series Accessories

SPORTSLIGHTING

ORDERING INFORMATION: SPORTSLITER® SYSTEM ACCESSORIES

Catalog Number	Description	Weight lbs. (kg)
4024SLS	Slipfitter for 2" (2 3/8" OD) tenon for integral luminaires	4 (1.8)
4024C ⁴	Slipfitter for 2" (2 3/8" OD) tenon for remote head units only	4 (1.8)
4090 ⁴	Heavy-duty cast iron crossarm fitting for horizontal trunnion for remote heads only	3 (1.4)
SLS-V2 ⁵	Visor assembly 12"	3 (1.4)
SLS-LV ⁶	Visor assembly 12" with external louvers	4 (1.9)
SLS-SPC ¹	Polycarbonate shield	5 (2.3)
SLS-AA-REM	Remote head aiming sight	-
FL-C3-14	3 ft. #14/3 SEOW-A cord	-
FL-C3-16	3 ft. #16/3 SEOW-A cord	-
FL-C6-14	6 ft. #14/3 SEOW-A cord	-
FL-C6-16	6 ft. #16/3 SEOW-A cord	-
SLSF	Field-installed single fuse holder (120, 277 & 347V)	-
SLSFF	Field-installed double fuse holder (208, 240 & 480V)	-
SLS5010 ²	Heavy-duty steel fitting	2 (0.9)
SLSC	Safety cable for integral luminaires	-
LR-30	Safety cable for remote yoke heads only	-

- Suitable for NEMA 5/6/W beam spreads; 400-1000w only
 - Must use with SLS Series (integral ballasted) when mounting on center location of TCA-W3 & TCA-R3 style crossarm brackets
 - For use with remote head only
 - Shipped with visor attached to lens ring assembly
 - Shipped with visor/louwer attached to lens ring assembly
- Note: For other mounting accessories, see floodlight mounting accessories (page 519)



ORDERING INFORMATION: SLS MOUNTING ACCESSORIES

Catalog Number	Maximum Loading		Description	Weight lbs. (kg)	EPA ft ² (m ²)
	Fixture Quantity	Weight lbs. (kg)			
Round Steel Pole - Crossarm Type - TCA-R Series - Clamps 3" to 5 1/2" dia.					
TCA-R2	2	210 (95.3)	For two fixtures	28 (12.7)	.8 (0.1)
TCA-R3 ¹	3	315 (142.9)	For three fixtures	70 (31.7)	1.6 (0.2)
TCA-R4	4	420 (190.5)	For four fixtures	106 (48)	2.5 (0.2)
Wood Pole - Crossarm Type - TCA-W Series - Thru or Lag Bolt (Not Included)					
TCA-W2	2	210 (95.3)	For two fixtures	21 (9.5)	1 (0.1)
TCA-W3 ¹	3	315 (142.9)	For three fixtures	80 (36.3)	1.8 (0.2)
TCA-W4	4	420 (190.5)	For four fixtures	106 (48)	2.4 (0.2)

- One SLS5010 mounting bracket included
- Note: Galvanized available, add suffix -M38

