



# 中国国家强制性产品认证证书

证书编号: 2024312313000615

## 认证委托人名称及地址

Hawke International (A Division of Hubbell Limited, A member of the Hubbell group of Companies)

Oxford Street West, Ashton-Under-Lyne, Lancashire, OL7 0NA, UK

## 生产者名称及地址

Hawke International (A Division of Hubbell Limited, A member of the Hubbell group of Companies)

Oxford Street West, Ashton-Under-Lyne, Lancashire, OL7 0NA, UK

## 生产企业名称及地址

Hawke International (A Division of Hubbell Limited, A member of the Hubbell group of Companies)

Oxford Street West, Ashton-Under-Lyne, Lancashire, OL7 0NA, UK

## 产品名称和系列、型号、规格

电缆引入装置

APEX E1F\*

Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da

## 产品标准和技术要求

GB/T 3836.1-2021, GB/T 3836.2-2021, GB/T 3836.3-2021, GB/T 3836.31-2021

上述产品符合《强制性产品认证实施规则 防爆电气》

(CNCA-C23-01: 2019) 的要求, 特发此证。

发证日期: 2024年04月26日 有效期至: 2029年04月25日

证书信息和有效性可扫描下方二维码或登录发证机构网站查验,  
也可在认监委网站 (www.cnca.gov.cn) 查询。



法定代表人:

南阳防爆电气研究所有限公司



# 中国国家强制性产品认证证书

证书编号：2024312313000615

证书附页：第 1 页 共 3 页

## 产品相关信息：

1、本证书覆盖产品如下：

— APEX E1F\*

本产品适用于编织覆盖层和铠装电缆，\*代表含义如下：

U=适用于编织覆盖层和铠装电缆

X=适用于编织覆盖层电缆

W=适用于铠装电缆

APEX E1F\*规格：

| 规格代码 | 螺纹类型    |        | 螺纹长度（最小） |       |
|------|---------|--------|----------|-------|
|      | M       | NPT    | M        | NPT   |
| 0s   | M16×1.5 | —      | 15.0     | —     |
|      | M20×1.5 |        |          |       |
| 0    | M16×1.5 | 1/2"   | 15.0     | 20.5  |
|      | M20×1.5 |        |          |       |
| A    | M20×1.5 | 1/2"   | 15.0     | 20.5  |
| B    | M25×1.5 | 3/4"   | 15.0     | 20.8  |
| C    | M32×1.5 | 1"     | 15.0     | 25.65 |
| C2   | M40×1.5 | 1 1/4" | 15.0     | 26.27 |
| D    | M50×1.5 | 1 1/2" | 15.0     | 26.69 |
| E    | M63×1.5 | 2"     | 15.0     | 27.53 |
| F    | M75×1.5 | 2 1/2" | 15.0     | 40.56 |
|      |         | 3"     |          | 42.15 |

APEX E1F\*型电缆引入装置用于圆形编织覆盖层和铠装电缆，包括以下组件：

a) 用于防护的垫圈（可选）

本页为证书附页，应与证书主页同时使用。



南阳防爆电气研究所有限公司





# 中国国家强制性产品认证证书

证书编号：2024312313000615

证书附页：第 2 页 共 3 页

b) 引入部分，尺寸范围 M16...M75, NPT1/2" ... NPT3"

c) 防洪涌密封（可选）

d) 内部可压缩密封圈

e) 隔膜套

f) 铠装夹紧环

g) 中间螺母

h) 外部可压缩密封圈

i) 滑环

j) 压紧螺母

外壳防护等级：IP66/IP67

防爆标志：Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da

— 生产者应按照认证机构批准的技术文件组织生产。

## 2、安全使用条件：

— 工作温度：-60℃~+130℃。

— 当用于增安型（气体环境）或防粉尘点燃外壳型（粉尘环境）外壳时，引入口螺纹应适当密封以满足相应外壳防护等级。

— 当用于导管或带编织覆盖层电缆时，仅适用于固定安装，其电缆必须被有效地夹紧，以防止拉力和扭矩。

— 其他见产品使用说明书。

本页为证书附页，应与证书主页同时使用。



南阳防爆电气研究所有限公司





# 中国国家强制性产品认证证书

证书编号：2024312313000615

证书附页：第3页 共3页

3、证书关联报告：

— 产品型式试验报告：CQST2401C017

4、证书变更信息：无

本页为证书附页，应与证书主页同时使用。



南阳防爆电气研究所有限公司

