

Certificate of Compliance

Certificate: 70013827

Project: 70013827 **Master Contract:** 151933

Date Issued:

April 21, 2015

Issued to:

3940 Dr. Martin Luther King Dr. St. Louis, MO 63113 USA Attention: Thomas J. Michalski

Killark Electric Manufacturing Co.

The products listed below are eligible to bear the CSA Mark shown with adjacent indicators 'C' and 'US' for Canada and US or with adjacent indicator 'US' for US only or without either indicator for Canada only.



Joe Dasílva

Issued by: Joe DaSilva

PRODUCTS

CLASS 4418 82 - OUTLET BOXES AND FITTINGS - Boxes - For Hazardous Locations -Certified to US Standards

CLASS 4418 02 - OUTLET BOXES AND FITTINGS - Boxes - For Hazardous Locations

Class II, Groups E, F and G; Class III, CSA Enclosures Type 4 or 4X IP66;

Ex tb/Zone 21 AEx tb, IIIC, T80°C/T100°C/T130°C Db

- SJIC*-JB, SJICH*-JB and USF*-JB Series Junction Boxes
- Cat. No. SPM followed by a five or six-digit number, maybe followed by additional letters and numbers.

Note - Enclosure Type 4 applies to enclosures fabricated from painted carbon steel while Enclosure Type 4X applies to enclosures fabricated from either stainless steel 304 or 316 grade.

CLASS 3218 06 - INDUSTRIAL CONTROL EQUIPMENT-Miscellaneous Apparatus - For Hazardous Locations

CLASS 3218 86 - INDUSTRIAL CONTROL EQUIPMENT-Miscellaneous Apparatus - For Hazardous Locations- Certified to U.S. Standards



 Certificate:
 70013827
 Master Contract:
 151933

 Project:
 70013827
 Date Issued:
 April 21, 2015

Cl. I, Div. 2, Gps. A, B, C, and D; Ex e/ Cl. I, Zone 1 AEx e IIC; CSA Encl. Type 4 or 4X, IP66; Ta = -50°C to +40°C (Temp. Code T6) or +55°C (Temp. Code T5) or +90°C(Temp. Code T4); Cl. II, Gps. E, F and G, Class III; Ex tb/Zone 21, AEx tb, IIIC, T80°C/T100°C/T130°C Db; CSA Encl. Type 4 or 4X, IP66;

- SJIC, SJICH and USF Series Terminal Boxes, Rated 600Vac (max) with wattage dissipation from 2Watts to 57.3 Watts for screw type terminals and from 1.0 Watts to 28.6 Watts max for cage clamp type terminals.
- Cat. No. SP followed by a letter, followed by a five or six-digit number, maybe followed by additional letters and numbers, Rated 600Vac (max) with wattage dissipation from 2Watts to 57.3 Watts for screw type terminals and from 1.0 Watts to 28.6 Watts max for cage clamp type terminals.

Note -

1/ Terminal boxes are provided with CSA certified and UL listed terminal assemblies and as such the electrical voltage rating and wire size range for the terminal boxes is limited to the CSA and UL certification listing of the terminal assemblies and the current and/or wattage rating maybe determined (Calculated) by the required temperature code rating so long as the current or wattage rating does not exceed the CSA and UL certification listing rating for the terminal assemblies, see manufactures installation instructions.

2/ Enclosure Type 4 applies to enclosures fabricated from painted carbon steel while Enclosure Type 4X applies to enclosures fabricated from either stainless steel 304 or 316 grade.

APPLICABLE REQUIREMENTS

CAN/CSA-C22.2 No 0-10	- General Requirements
CAN/CSA-C22.2 No 14-13	- Industrial Control Equipment
CAN/CSA-C22.2 No 25-1966 Locations	- Enclosures for Use in Class II, Groups E, F and G Hazardous
CAN/CSA-C22.2 No 94-M91	- Special Purpose Enclosures
CAN/CSA-C22.2 No 213-M1987 Hazardous Locations	- Non-incendive Electrical Equipment for Use in Class I, Division 2
ANSI/UL Standard No. 50E:2007 Considerations	- Enclosures for Electrical Equipment, Environmental
ANSI/UL Standard No. 508A:2013	- Industrial Control Panels



Certificate:	70013827	Master Contract:	151933
Project:	70013827	Date Issued:	April 21, 2015

ANSI/UL Standard No. 1203:2013 Use in Hazardous (Classified) Locations	- s	Explosion-Proof and Dust-Ignition-Proof Electrical Equipment for
ANSI/ISA-12.12.01-2013 II, Division 2 and Class III, Divisions 1	- and	Non-incendive Electrical Equipment for Use in Class I and Class I 2 Hazardous Locations
CAN/CSA 60079-0:11	-	Explosive Atmospheres- Part 0: General Requirements
CAN/CSA 60079-7:12 safety "e"	-	Explosive Atmospheres- Part 7: Equipment protection by increased
CAN/CSA 60079-31:12 protection by enclosure "t"	-	Explosive Atmospheres- Part 31: Equipment dust ignition
CAN/CSA 60529:05	-	Degrees of Protection
ANSI/ISA 60079-0:13	-	Explosive Atmospheres- Part 0: General Requirements
ANSI/ISA 60079-7:13 safety "e"	-	Explosive Atmospheres- Part 7: Equipment protection by increased
ANSI/ISA 60079-31:09 protection by enclosure "t"	-	Explosive Atmospheres- Part 31: Equipment dust ignition
ANSI/IEC 60529-2004	-	Degrees of Protection Provided by Enclosure (IP Code)