

NOTES:

VOLTAGE RANGE AC: 90-254VAC

OUTPUT VOLTAGE: 12VDC (10-16 ADJ)

AMP RATING: 4.5-3.4A

OUTPUT POWER: 54W

EFFICIENCY: 86%


OPERATING TEMP.: -10°C TO +60°C

FREQUENCY: 47-63Hz

PROPRIETARY AND CONFIDENTIAL

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ACME ELECTRIC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF ACME ELECTRIC IS PROHIBITED.

DO NOT SCALE DRAWING

	NAME	DATE	 <p><b>Acme Electric</b> MENOMONEE FALLS, WI 53051 USA</p>		
DRAWN	AJP	11-21-17			
CHECKED	AJP	11-21-17			
ENG APPR.	AJP	11-21-17			
SCALE: 1:2			TITLE: SINGLE PHASE		
SHEET 1 OF 1			SIZE	DWG. NO.	REV
			<b>B</b>	DM112045	<b>A</b>