



NOTES:

VOLTAGE RANGE AC: 90-254VAC

OUTPUT VOLTAGE: 24VDC (22-28 ADJ)

AMP RATING: 20.0-17.1A

OUTPUT POWER: 480W

EFFICIENCY: 90%

OPERATING TEMP.: -10°C TO +60°C

FREQUENCY: 47-63Hz

PROPRIETARY AND CONFIDENTIAL

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ACME ELECTRIC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF ACME ELECTRIC IS PROHIBITED.

DO NOT SCALE DRAWING

| | | | | |
|--------------|------|------------------|--|-----------------|
| | NAME | DATE |  Acme Electric® MENOMONEE FALLS, WI 53051 USA | |
| DRAWN | AJP | 11-21-17 | | |
| CHECKED | AJP | 11-21-17 | | |
| ENG APPR. | AJP | 11-21-17 | | |
| SCALE: 1:2 | | | TITLE: SINGLE PHASE | |
| SHEET 1 OF 1 | | SIZE B | DWG. NO. DM12420 | REV A |