

**NOTES:**

VOLTAGE RANGE AC: 90-264VAC

OUTPUT VOLTAGE: 12VDC (10-14 ADJ)


AMP RATING: 1.25-1.07A

OUTPUT POWER: 15W

EFFICIENCY: 78%

OPERATING TEMP.: -10°C TO +50°C

FREQUENCY: 47-63Hz

	NAME	DATE	 <p><b>Acme Electric</b><sup>®</sup> MENOMONEE FALLS, WI 53051 USA</p>	
DRAWN	AJP	11-21-17		
CHECKED	AJP	11-21-17		
ENG APPR.	AJP	11-21-17		
<p><b>SCALE: 1:2</b></p>			TITLE: PLASTIC	
SHEET 1 OF 1		SIZE <b>B</b>	DWG. NO. DMP1120125	REV <b>A</b>

**PROPRIETARY AND CONFIDENTIAL**  
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ACME ELECTRIC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF ACME ELECTRIC IS PROHIBITED.  
DO NOT SCALE DRAWING