

NOTES:

VOLTAGE RANGE AC: 90-264VAC

OUTPUT VOLTAGE: 12VDC (10-14 ADJ)

AMP RATING: 3.0-2.14A


OUTPUT POWER: 30W

EFFICIENCY: 84%

OPERATING TEMP.: -10°C TO +50°C

FREQUENCY: 47-63Hz

PROPRIETARY AND CONFIDENTIAL
 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ACME ELECTRIC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF ACME ELECTRIC IS PROHIBITED.
 DO NOT SCALE DRAWING

	NAME	DATE	 Acme Electric [®] MENOMONEE FALLS, WI 53051 USA
DRAWN	AJP	11-21-17	
CHECKED	AJP	11-21-17	
ENG APPR.	AJP	11-21-17	
TITLE:			PLASTIC
SCALE: 1:2		SIZE	REV
SHEET 1 OF 1		DWG. NO.	DMP112025
			A