



NOTES:

VOLTAGE RANGE AC: 90-264VAC

OUTPUT VOLTAGE: 5VDC (4.5-5.5 ADJ)

AMP RATING: 4.4-3.64A

OUTPUT POWER: 20W

EFFICIENCY: 75%

OPERATING TEMP.: -10°C TO +50°C

FREQUENCY: 47-63Hz

	NAME	DATE	 <p>Acme Electric MENOMONEE FALLS, WI 53051 USA</p>		
DRAWN	AJP	11-21-17			
CHECKED	AJP	11-21-17			
ENG APPR.	AJP	11-21-17			
<p>PROPRIETARY AND CONFIDENTIAL</p> <p>THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ACME ELECTRIC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF ACME ELECTRIC IS PROHIBITED.</p> <p>DO NOT SCALE DRAWING</p>			<p>TITLE: PLASTIC</p>		
<p>SCALE: 1:2</p>			SIZE	DWG. NO.	REV
<p>SHEET 1 OF 1</p>			B	DMP1504	A