


OUTPUT CONNECTIONS (NOTE 3)



- NOTES:
- 1. CONTACTS SHOWN IN NO POWER CONDITION, PUMP OFF.
 - 2. INPUT CONNECTIONS REQUIRE DRY CONTACTS.
 - 3. OUTPUT CONNECTIONS ARE CONTACTS RATED FOR PILOT DUTY ONLY.
 - 10 AMPS AT 250 VOLTS-AC MAXIMUM LOAD.
 - 4 AMPS AT 12 VOLTS-DC MAXIMUM LOAD.
 - 4. EXTERNAL CONTROL WIRE #16 GA. AWG MAXIMUM.
 - 5. CUSTOMER CONNECTIONS ARE SHOWN BY MEANS OF DASH LINES.

REV/DATE/BY	DESCRIPTION	DRAWN	DRAWN	11-18-15
05/15/17	CHANGED BOARD PART NOS;	CHECKED	APPROVED	11-18-15
A	ELIMINATED POWER COMMS HUB	APPD	APPROVED	11-18-15
DAMA				
FIELD CONNECTIONS, MODEL MPT300 ACROSS-THE-LINE START ELECTRIC FIRE PUMP CONTROLLER				
OPTIONS:				
HCMP TF300				
SCALE NTS				SHEET 1 OF 2