


12 CHANNEL IO  
P/N HC90776002

## OUTPUT CONNECTIONS (NOTE 3)

## INPUT CONNECTIONS (NOTE 2)

NOTES:

1. CONTACTS SHOWN IN NO POWER CONDITION, PUMP OFF.
2. INPUT CONNECTIONS REQUIRE DRY CONTACTS.
3. OUTPUT CONNECTIONS ARE CONTACTS RATED FOR PILOT DUTY ONLY.  
10 AMPS AT 250 VOLTS-AC MAXIMUM LOAD.
4. AMPS AT 12 VOLTS-DC MAXIMUM LOAD.
4. EXTERNAL CONTROL WIRE #16 GA AWG MAXIMUM.
5. CUSTOMER CONNECTIONS ARE SHOWN BY MEANS OF DASH LINES.

REV	DATE / BY	DESCRIPTION	DRAWN	DRAWN	11-18-15
A	05/15/17 DAMA	CHANGED BOARD PART NOS.; ELIMINATED POWER COMMS HUB	CHECKED	CHECKED	11-18-15
			APPD	APPROVED	11-18-15
FIELD CONNECTIONS, MODEL MPT450 AUTOTRANSFORMER CLOSED TRANSITION START ELECTRIC FIRE PUMP CONTROLLER					
HUBBELL			 <b>METRON</b> A Division of Hubbell Industrial Controls, Inc. 4301 Cheyenne Drive, Archdale, NC 27263 USA		
OPTIONS:			HCMPPT450  SCALE NTS SHEET 1 OF 2		

2

I