



ALT. SOURCE
POWER OPERATOR




FRONT VIEW

CIRCUIT BREAKER/
ISOLATION SWITCH
OPERATOR




SIDE VIEW




BOTTOM VIEW

PILOT DEVICE LEGEND
LEFT FLANGE

- L1. SWITCH IN EMERGENCY LIGHT
- L2. PUSH TO TEST BUTTON
- L3. SWITCH IN NORMAL LIGHT
- L4. EMERGENCY ISO SW. OPEN LIGHT




PILOT DEVICE DETAIL
LEFT FLANGE



PILOT DEVICE LEGEND
RIGHT FLANGE

- R1. START PUSH BUTTON
- R2. STOP PUSH BUTTON
- R3. POWER ON LIGHT
- R4. PHASE REVERSAL LIGHT



PILOT DEVICE DETAIL
RIGHT FLANGE

VOLTAGE	HORSEPOWER
200V	200-250 HP.
208V	200-250 HP.
230V	250 HP.
380V, 415V	350 HP.
460V	500 HP.

NOTES:
ALL DIMENSIONS IN INCHES
AND MILLIMETERS ([])

ENCLOSURE DIMENSIONS MODEL M300 WITH TRANSFER SWITCH 97.25" CABINET, 18" DEEP ELECTRIC FIRE PUMP CONTROLLER	DRAWN	FR	2-10-98	METRON, INC. DENVER, CO.
	CHECK	KH	2-21-98	
	APPD	J.S.	2-21-98	
				CD32955A
SCALE				N.T.S. SHEET 1 OF 1