



- PILOT DEVICE LEGEND
LEFT FLANGE**
- L1. SWITCH IN EMERGENCY LIGHT
 - L2. PUSH TO TEST BUTTON
 - L3. SWITCH IN NORMAL LIGHT
 - L4. EMERGENCY ISO SW. OPEN LIGHT



- PILOT DEVICE LEGEND
RIGHT FLANGE**
- R1. START PUSH BUTTON
 - R2. SOFT STOP PUSH BUTTON
 - R3. POWER ON LIGHT
 - R4. COAST STOP PUSH BUTTON
 - R5. PHASE REVERSAL LIGHT
 - R6. DRIVE FAULT LIGHT

VOLTAGE	HORSEPOWER
200V	50-150 HP.
208V	50-150 HP.
230V	60-200 HP.
380V, 415V	100-300 HP.
460V	125-400 HP.

NOTES:
ALL DIMENSIONS IN INCHES AND MILLIMETERS ()

DRAWN SR 2-10-98 CHECK KH. 2-21-98 APPD J.C. 2-21-98	METRON, INC. DENVER, CO.		
		ENCLOSURE DIMENSIONS MODEL M700 W/TRANSFER SWITCH 64" CABINET ELECTRIC FIRE PUMP CONTROLLER	
		CD32937B	SCALE N.T.S. SHEET 1 OF 1